

CC-DT-H 15/49 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

We support our customers in the food industry with detectable marking solutions to ensure the high standards required within the framework of the HACCP concept. Thanks to a metallic filler, our detectable MultiCards can be reliably identified by metal and X-ray detectors. This minimises the risk of product contamination in the production process. Maximum safety is ensured with important product properties, such as corrosion resistance or higher ageing resistance to UV radiation in indoor areas and heat. These properties are regularly tested and confirmed in our own accredited laboratory. Not suitable for direct food contact.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler
- Clear and resistant print image
- Available in different versions for a wide variety of marking requirements

General ordering data

Version	ClipCard, Accessories, 17 x 52 mm, blue
Order No.	3009100000
Type	CC-DT-H 15/49 BL
GTIN (EAN)	4099986911680
Qty.	25 items

CC-DT-H 15/49 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	17 mm	Height (inches)	0.6693 inch
Width	52 mm	Width (inches)	2.0472 inch
Length	49 mm	Length (inches)	1.9291 inch
Diameter	0 mm	Net weight	1.77 g

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.027 kg CO2 eq.	

General data

Version	Marker holder	Width	52 mm
UL 94 flammability rating	HB	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Colour	blue
Halogen	No	Length	49 mm
Basic material	Polyamide 66	Detectible in accordance with Rondotest	4.7 mm Al
Recommended industries	Food processing industry	Operating temperature range	-40...100 °C

Device markers

Diameter	0 mm	Halogen	No
----------	------	---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

