

VPU PV I+II 5 1500

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	3012980000
Type	VPU PV I+II 5 1500
GTIN (EAN)	4099986922587
Qty.	1 items

VPU PV I+II 5 1500

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	86 mm	Depth (inches)	3.3858 inch
Height	96.5 mm	Height (inches)	3.7992 inch
Width	90 mm	Width (inches)	3.5433 inch
Net weight	760 g		

Temperatures

Storage temperature	-40 °C...85 °C	Ambient temperature	-40 °C...85 °C
Operating temperature	-40 °C...85 °C	Humidity	5 - 95% rel. humidity

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Optical function display	green = OK; red = arrester is defective - replace	Version	Surge protection I / II
Design	Installation housing, 5 TE, Insta IP 20	UL 94 flammability rating	V-0
Colour	orange, black	Suitable for	Photovoltaics
Protection degree	IP20 in installed state, IP20	Mounting rail	TS 35
Operating altitude	≤ 4000 m		

Insulation coordination acc. to EN 50178

Surge voltage category	I, III	Pollution severity	2
------------------------	--------	--------------------	---

Photovoltaic technical data

Standards	EN 61643-31, EN 50539-11	Lightning test current limp (10/350 μs)	5 kA
Protection level Up (+/-, -/PE, +/-PE)	≤ 5,0 kV	Operating height in ungrounded PV system	≤ 4000 m
Short-circuit current ISCPV	11000 A	Total discharge current I _{total} (8/20 μs)	50 kA
Discharge current I _n (8/20 μs)	20 kA	Requirements class	Type I/II
Operating height in the grounded PV system	≤ 2000 m	Total discharge current I _{total} (10/350 μs)	10 kA
Protection level Up (+/-)	≤ 5,0 kV	PV system voltage, max. U _{cpv}	1500 V

Rated data IEC / EN

Number of poles	5	Leakage current at U _n	30 μA
Signalling contact	No	Rated voltage (DC)	1500 V

VPU PV I+II 5 1500

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Voltage type	DC	Response time / fallback time	≤ 25 ns
Suitable for	Photovoltaics	Standards	EN 61643-31, EN 50539-11
Lightning test current limp (10/350 μs)	5 kA	Max. continuous voltage, U _c (DC)	1500 V
Energy coordination (≤10 m)	Type I, Type II, Type III	Discharge current I _{max} (8/20μs) wire-PE	30 kA
SPD type	T2, T1	Short-circuit current rating ISCCR	50 kA
Integrated back-up fuse	No		

Connection data

Stripping length	18 mm	Wire connection method	Screw connection
Stripping length, rated connection	18 mm	Tightening torque, min.	3 Nm
Tightening torque, max.	4.5 Nm	Clamping range, rated connection	6 mm ²
Clamping range, min.	1.5 mm ²	Clamping range, max.	35 mm ²
Wire cross-section, solid, min.	1.5 mm ²	Wire cross-section, solid, max.	35 mm ²
Wire connection cross section, finely stranded, max.	35 mm ²	Connection cross-section, stranded, min.	1.5 mm ²
Connection cross-section, stranded, max.	35 mm ²		

Electrical data

Voltage type	DC
--------------	----

General data

Number of poles	5	Protection degree	IP20 in installed state, IP20
Colour	orange, black		


Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 8.0	EC001457	ETIM 9.0	EC001457
ETIM 10.0	EC001457	ECLASS 14.0	27-17-14-03
ECLASS 15.0	27-17-14-03		

Drawings



VPU PV I+II 5 1500

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Crosshead screwdriver Phillips



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH1 X 80	Version	
Order No.	2749890000	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1	
GTIN (EAN)	4050118897098		
Qty.	1 ST		

Slotted screwdriver




VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Type	SDIS 1.0X5.5X125	Version	
Order No.	2749850000	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade thickness (A): 1 mm	
GTIN (EAN)	4050118897050		
Qty.	1 ST		

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

VPU PV I+II 5 1500

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	ESG 6/15 K MC NE WS	Version	
Order No.	188010000	ESG, Device markers x 15 mm, PA 66, Colour: white, Self-adhesive	
GTIN (EAN)	4032248478781		
Qty.	200 ST		

VPU Series



Extensive accessories round off the product range

General ordering data

Type	VPU PV EXTENDER	Version	
Order No.	312351000		
GTIN (EAN)	4099987270199		
Qty.	9 ST		

Spare Arrester



General ordering data

Type	VPU PV I+II 5 0 1500	Version	
Order No.	301302000		
GTIN (EAN)	4099986922617		
Qty.	9 ST		
Type	VPU PV I+II 5 0M 1500	Version	
Order No.	301301000		
GTIN (EAN)	4099986922600		
Qty.	9 ST		

VPU PV I+II 5 1500

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

VPU Series



Extensive accessories round off the product range

General ordering data

Type	VPU LOCKING CLIP L	Version	
Order No.	2735070000		
GTIN (EAN)	4050118816402		
Qty.	10 ST		