

DURA MAX DC UPS 24V 10A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



The UPS control unit together with the associated battery module and the power supply unit form a complete DC UPS system. In normal operation, the input voltage from the UPS control unit is connected directly to the load. In the event of a mains failure (drop of the DC input voltage) the system switches instantly to battery operation. Once the mains supply has been restored, the system switches back to normal operation and the battery is fully recharged by the integrated charger.

Three relay outputs, as well as three additional active transistor outputs and a control input to lock battery operation, provide full remote control by means of SPS or DCS control. Numerous modes of operation and an easy-to-use status display provide rapid fault diagnosis and optimum customisation to the application.

General ordering data

Version	UPS control unit, 24 V
Order No.	2934950000
Type	DURA MAX DC UPS 24V 10A
GTIN (EAN)	4099986684096
Qty.	1 items

DURA MAX DC UPS 24V 10A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	125 mm	Depth (inches)	4.9212 inch
Height	130 mm	Height (inches)	5.1181 inch
Width	30 mm	Width (inches)	1.1811 inch
Net weight	483 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Humidity	5...95 %, no condensation		

Battery module

Nominal voltage	24 V
-----------------	------

Integrated battery charger

Temperature coefficient	- 48 mV / °C	Charging voltage (temperature compensated)	27, 48 V @ 20°C
Battery availability test	every minute	Charging feature	IU characteristic curve

Operating interfaces and control inputs

Selector switch buffer times	0.5 min, 1 min, 3 min, 10 min, 20 min, 30 min, Service	Temperature probe	NTC 100 kΩ
Remote disconnection (Interlock)	Yes	Selector switch battery	1.2 Ah, 3.4 Ah, 7 Ah, 12 Ah

Input

Rated input voltage	24 V DC	Wire connection method	PUSH IN
Input fuse (internal)	Yes	DC current consumption	<0.2 A @ no load
DC input voltage range	18...30 V DC	Input current	<10.2 A
Inrush Current Limitation	<28 A		

Output

Output power	240 W	Rated output voltage	24 V DC
Parallel connection option	yes, max. 2	Output current, max.	10 A
Wire connection method	PUSH IN	Output voltage type	DC
Temperature coefficient	- 48 mV / °C	Battery charging current	0.5 A (3.4 AH)
Temperature probe	NTC 100 kΩ	Protection against inverse voltage	Yes

General data

Degree of efficiency	> 98%	Weight	500 g
Humidity	5...95 %, no condensation	Protection degree	IP20
Mounting position, installation notice	On TS 35 mounting rail, 50 mm clearance above	Housing version	Metal, corrosion resistant

DURA MAX DC UPS 24V 10A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

	and below for free air supply.		
Protection against reverse voltages from the load	≤ 35 V DC	Power loss	<10 W
Storage medium	3.4 Ah, 12 Ah, Selectable with rotary switch, 1.2 Ah, 7 Ah	Clip-in foot	metal
Short-circuit protection	Yes	Buffer times	Depending on the connected battery

EMC / shock / vibration

Shock resistance IEC 60068-2-27	30 g in all directions	Noise emission in accordance with EN55032	Class B
Interference immunity test acc. to	EN 61000-4-2 (ESD)/ EN 61000-4-3 and EN 61000-4-8 (fields)/EN 61000-4-4 (burst)/EN 61000-4-5 (surge)/EN 61000-4-6 (conducted)/ EN 61000-4-11 (dips)	Vibration resistance IEC 60068-2-6	2.3 g, 4 g

Insulation coordination

Pollution severity	2	Insulation voltage	1 kV DC
Protection class	III		

Electrical safety (applied standards)

For use with electronic equipment	Acc. to EN50178	Electrical machine equipment	Acc. to EN60204
Safety transformers for switch-mode power supplies	According to EN 61558-2-16		

Connection data (input)

Reverse polarity protection	Yes	Conductor cross-section, AWG/kcmil , max.	14 AWG
Conductor cross-section, AWG/kcmil , min.	16 AWG	Wire connection cross section, flexible (input), max.	2.5 mm ²
Conductor cross-section, flexible , min.	1.5 mm ²	Conductor cross-section, rigid , max.	2.5 mm ²
Conductor cross-section, rigid , min.	1.5 mm ²		

Connection data (output)

Reverse polarity protection	Yes	Conductor cross-section, AWG/kcmil , max.	14 AWG
Conductor cross-section, AWG/kcmil , min.	16 AWG	Conductor cross-section, flexible , max.	2.5 mm ²
Conductor cross-section, flexible , min.	1.5 mm ²	Conductor cross-section, rigid , max.	2.5 mm ²
Conductor cross-section, rigid , min.	1.5 mm ²		

Connection data (signal)

Wire connection cross-section, flexible (signal), max.	1.5 mm ²	Wire connection method	PUSH IN
Wire cross-section, AWG/kcmil , max.	16	Wire cross-section, solid , min.	0.2 mm ²
Wire cross-section, solid , max.	1.5 mm ²	Wire connection cross-section, flexible (signal), min.	0.2 mm ²
Wire cross-section, AWG/kcmil , min.	25 mm ²		

DURA MAX DC UPS 24V 10A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Signalling

Status indicator	LED red: Battery fault, LED yellow: Alarm/ Temperature Sensor fault, LED green: Normal mode, LED green flashing: Buffer mode, LED off: no error	Floating contact	Yes
------------------	--	------------------	-----

Classifications

ETIM 8.0	EC002850	ETIM 9.0	EC002850
ETIM 10.0	EC002850	ECLASS 14.0	27-04-06-92
ECLASS 15.0	27-04-06-92		