

DURA MAX DC UPS 24V 20A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The UPS control unit together with the associated battery module and the power supply unit form a complete DC UPS system. In normal operation, the input voltage from the UPS control unit is connected directly to the load. In the event of a mains failure (drop of the DC input voltage) the system switches instantly to battery operation. Once the mains supply has been restored, the system switches back to normal operation and the battery is fully recharged by the integrated charger.

Three relay outputs, as well as three additional active transistor outputs and a control input to lock battery operation, provide full remote control by means of SPS or DCS control. Numerous modes of operation and an easy-to-use status display provide rapid fault diagnosis and optimum customisation to the application.

General ordering data

Version	UPS control unit, 24 V
Order No.	2934960000
Type	DURA MAX DC UPS 24V 20A
GTIN (EAN)	4099986684102
Qty.	1 items

DURA MAX DC UPS 24V 20A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E258476
Certificate no. (cULusEX)	E470829

Dimensions and weights

Depth	125 mm	Depth (inches)	4.9212 inch
Height	130 mm	Height (inches)	5.1181 inch
Width	38 mm	Width (inches)	1.4961 inch
Net weight	575 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Humidity	5...95 %, no condensation		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1, Diboron trioxide 1303-86-2, Lead monoxide 1317-36-8
SCIP	596c610a-7280-4711-937f-d77f7dbaa5e7

Battery module

Nominal voltage	24 V
-----------------	------

Integrated battery charger

Temperature coefficient	- 48 mV / °C	Charging voltage (temperature compensated)	27, 48 V @ 20°C
Battery availability test	every minute	Charging feature	IU characteristic curve

Operating interfaces and control inputs

Selector switch buffer times	0.5 min, 1 min, 3 min, 10 min, 20 min, 30 min, Service	Temperature probe	NTC 100 kΩ
Remote disconnection (Interlock)	Yes	Selector switch battery	3.4 Ah, 7 Ah, 12 Ah, 17 Ah, 26 Ah

Input

Rated input voltage	24 V DC	Wire connection method	PUSH IN
Input fuse (internal)	Yes	DC current consumption	<0.2 A @ no load
DC input voltage range	18...30 V DC	Input current	≤26 A
Inrush Current Limitation	< 28 A		

DURA MAX DC UPS 24V 20A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com
Technical data**Output**

Output power	480 W	Rated output voltage	24 V DC
Parallel connection option	yes, max. 2	Overload protection	Yes
Output voltage, max.	29.5 V	Output voltage, min.	17.5 V
Output current, max.	20 A	Wire connection method	PUSH IN
Output voltage type	DC	Temperature coefficient	- 48 mV / °C
Battery charging current	0.5 A (3.4 AH)	Temperature probe	NTC 100 kΩ
Protection against inverse voltage	Yes		

General data

Degree of efficiency	> 98%	
Weight	600 g	
Humidity	5...95 %, no condensation	
Protection degree	IP20	
Surge voltage category	III	
Mounting position, installation notice	On TS 35 mounting rail, 50 mm clearance above and below for free air supply.	
Housing version	Metal, corrosion resistant	
Protection against reverse voltages from the load	≤ 35 V DC	
Power loss	< 10 W	
MTBF	Operating time (hours), min.	700000 h
	Ambient temperature	25 °C
	Input voltage	24 V
	Duty cycle	100 %
Storage medium	3.4 Ah, 7 Ah, 12 Ah, 17 Ah, Selectable with rotary switch	
Clip-in foot	metal	
Short-circuit protection	Yes	
Buffer times	Depending on the connected battery	

EMC / shock / vibration

Shock resistance IEC 60068-2-27	30 g in all directions	Noise emission in accordance with EN55032	Class B
Interference immunity test acc. to	EN 61000-4-2 (ESD)/ EN 61000-4-3 and EN 61000-4-8 (fields)/EN 61000-4-4 (burst)/EN 61000-4-5 (surge)/EN 61000-4-6 (conducted)/ EN 61000-4-11 (dips)	Vibration resistance IEC 60068-2-6	2.3 g, 4 g

Insulation coordination

Surge voltage category	III	Pollution severity	2
Insulation voltage	1 kV DC	Protection class	III

Electrical safety (applied standards)

For use with electronic equipment	Acc. to EN50178	Electrical machine equipment	Acc. to EN60204
Safety transformers for switch-mode power supplies	According to EN 61558-2-16		

DURA MAX DC UPS 24V 20A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Connection data (input)**

Reverse polarity protection	Yes	Conductor cross-section input (AWG), max.	10 AWG
Conductor cross-section (AWG) (input), min.	12 AWG	Wire connection cross-section, flexible (input), max.	2.5 mm ²
Conductor cross-section, flexible , min.	4 mm ²	Conductor cross-section, rigid , max.	6 mm ²
Conductor cross-section, rigid , min.	4 mm ²		

Connection data (output)

Reverse polarity protection	Yes	Conductor cross-section (AWG) (output), max.	10 AWG
Conductor cross-section (AWG) (output) , min.	12 AWG	Conductor cross-section, flexible , max.	6 mm ²
Conductor cross-section, flexible , min.	4 mm ²	Conductor cross-section, rigid , max.	6 mm ²
Conductor cross-section, rigid , min.	4 mm ²		

Connection data (signal)

Wire connection cross-section, flexible (signal), max.	1.5 mm ²	Wire connection method (signal)	PUSH IN
Wire cross-section (AWG) (signal), max.	16	Wire cross-section, solid (signal), min.	0.2 mm ²
Wire cross-section, solid (signal), max.	1.5 mm ²	Wire connection cross-section, flexible (signal), min.	0.2 mm ²
Wire cross-section (AWG) (signal), min.	25 mm ²		

Signalling

Status indicator	LED red: Battery fault, LED yellow: Alarm/ Temperature Sensor fault, LED green: Normal mode, LED green flashing: Buffer mode, LED off: no error	Floating contact	Yes
------------------	--	------------------	-----


Classifications

ETIM 8.0	EC002850	ETIM 9.0	EC002850
ETIM 10.0	EC002850	ECLASS 14.0	27-04-06-92
ECLASS 15.0	27-04-06-92		

DURA MAX DC UPS 24V 20A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Blade fuses****General ordering data**

Type	CP A FUSE 15A	Version
Order No.	2582100000	UPS control unit
GTIN (EAN)	4050118699708	
Qty.	2 ST	
Type	CP A FUSE 25A	Version
Order No.	2582110000	UPS control unit
GTIN (EAN)	4050118809756	
Qty.	2 ST	