

**SAIE-M12SK-5-0.2VHM16-1.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

**General ordering data**

Version	Built-in plugs, M12, male, pin, straight, Mounting thread: M 16 x 1.5, Number of poles: 5, Strand / cable length: 0.2 m, Rear panel mounting
Order No.	<a href="#">2968020000</a>
Type	SAIE-M12SK-5-0.2VHM16-1.5
GTIN (EAN)	4099986779426
Qty.	1 items

## SAIE-M12SK-5-0.2VHM16-1.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E310075

### Dimensions and weights

Net weight	25 g
------------	------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

### Technical specifications for cable

PE function	Yes	Core cross-section	1.5 mm <sup>2</sup>
Strand / cable length	0.2 m	Colour coding	black, brown, grey, blue, Green/yellow
Number of poles	5 (4 + PE)		

### Technical data customisable plug-in connectors

Number of poles	5	Coding	K-coded
Contact surface	Gold-plated	Housing main material	Zinc diecast
Insulation resistance	≥ 100 MΩ	Nominal voltage	630 V
Nominal current	12 A	Protection degree	IP65, IP67, IP68, when screwed in
Plugging cycles	≥ 100	Pollution severity	3
Temperature range of housing	-40 ... +85 °C		

### Standards

Connector standard	IEC 61076-2-111
--------------------	-----------------

### General data

Number of poles	5
Coding	K-coded
Connection thread	M12
Contact surface	Gold-plated
Tightening torque	1 Nm
Core cross-section	1.5 mm <sup>2</sup>
Housing main material	Zinc diecast
Insulation resistance	≥ 100 MΩ
Type of mounting	Rear panel mounting
Nominal voltage	630 V
Nominal current	12 A
AF size	19 mm
Protection degree	IP65, IP67, IP68, when screwed in

**SAIE-M12SK-5-0.2VHM16-1.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**


Plugging cycles	≥ 100
Pollution severity	3
Connection 1	M12
Connection 2	Flying wires
Strand / cable length	0.2 m
Mounting thread	M 16 x 1.5
Mounting torque range	2 Nm
Mounting torque	max. 2 Nm
Temperature range of housing	-40 ... +85 ° C

**Classifications**


ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		

**Drawings**


**Dimensioned drawing**




**Dimensioned drawing**



**Pole scheme**



**Wiring diagram**



**Detailed drawing**

