


**THM PV 30/60 TR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



UV-radiation causes high stress and aging of plastic in the outdoor application.

Our new THM PV labels resist these influences and are extremely durable in outdoor use.

Compact designed packaging are our TABPACK-PV.

These are-printed warning labels, which should be a part of the basic equipment of a professional photovoltaic builder.

Your advantages at a glance:

- Weathering resistance tested according to ISO DIN EN ISO 4892-2:2013 table 3, procedure A cycle 1 at 5000 hours
- Individually labeled with the M-Print® PRO
- Easy and fast printing with the THM MultiMark

**General ordering data**

Version	ClipCard, Device markers, 29.6 x 59.6 mm, Transparent
Order No.	<a href="#">2969130000</a>
Type	THM PV 30/60 TR
GTIN (EAN)	4099986783782
Qty.	450 items
Packaging	Reel

**THM PV 30/60 TR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	29.6 mm	Height (inches)	1.1654 inch
Width	59.6 mm	Width (inches)	2.3465 inch
Net weight	0.33 g		

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Adhesive	Polyacrylate adhesive	Type of printing	neutral
Printing method	Thermal transfer	Version	Self-adhesive
Width	59.6 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	-50 °C	Operating temperature range, min.	110 °C
Colour	Transparent	Halogen	Yes
Basic material	Vinyl film	Printed characters	without
Number per roll	450		

**Conductor and cable markers**

Halogen Yes

**Device markers**

Halogen Yes

**Classifications**

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**Drawings**

