


**SDT 2.5 4C BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

In some applications it makes sense to add a test point or a disconnect element to the feed through terminal for testing and safety purposes. With test disconnect terminals you measure electric circuits in the absence of voltage. While the disconnecting points clearance and creepage distance is not assessed in dimensional terms, the specified rated impulse voltage strength must be proven.

**General ordering data**

|            |   |
|------------|---|
| Version    | Test-disconnect terminal, SNAP IN, blue, 2.5 mm <sup>2</sup> , 20 A, 500 V, Number of connections: 4, Number of levels: 1 |
| Order No.  | <a href="#">2974170000</a>  |
| Type       | SDT 2.5 4C BL   |
| GTIN (EAN) | 4099986801547   |
| Qty.       | 50 items  |

## SDT 2.5 4C BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



UL File Number Search

[UL Website](#)

Certificate No. (cURus)

E60693

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 37.65 mm | Depth (inches)  | 1.4823 inch |
| Height     | 96 mm    | Height (inches) | 3.7795 inch |
| Width      | 5.1 mm   | Width (inches)  | 0.2008 inch |
| Net weight | 10.23 g  |                 |             |

## Temperatures

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## Material data

|                                |        |                           |      |
|--------------------------------|--------|---------------------------|------|
| Basic material                 | Wemid  | Colour                    | blue |
| Colour of operational elements | orange | UL 94 flammability rating | V-0  |

## Rating data IECEx/ATEX

|                                |                     |                         |                  |
|--------------------------------|---------------------|-------------------------|------------------|
| Certificate No. (ATEX)         | TUEV24ATEX9191U     | Certificate No. (IECEX) | IECEXTUR24.0071U |
| Max. voltage (ATEX)            | 550 V               | Current (ATEX)          | 19 A             |
| Wire cross section max. (ATEX) | 2.5 mm <sup>2</sup> | Max. voltage (IECEX)    | 550 V            |
| Current (IECEX)                | 19 A                |                         |                  |

## System specifications

|                                     |     |                                   |       |
|-------------------------------------|-----|-----------------------------------|-------|
| End cover plate required            | Yes | Number of levels                  | 1     |
| Number of clamping points per level | 4   | Levels cross-connected internally | No    |
| PE connection                       | No  | Mounting rail                     | TS 35 |
| N-function                          | No  | PE function                       | No    |
| PEN function                        | No  |                                   |       |

## Additional technical data

|                  |         |                          |     |
|------------------|---------|--------------------------|-----|
| Open sides       | right   | Snap-on                  | Yes |
| Type of fixing   | Snap-on | Explosion-tested version | No  |
| Type of mounting | Snap-on |                          |     |

## Conductors for clamping (rated connection)

|                      |     |   |        |
|----------------------|-----|---|--------|
| Gauge to IEC 60947-1 | A3  | Wire connection cross section AWG, max. | AWG 14 |
| Connection direction | top | Stripping length                        | 10 mm  |

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

|   |                      |   |                      |
|---|----------------------|---|----------------------|
| Type of connection 2  | SNAP IN              | Type of connection  | SNAP IN              |
| Number of connections   | 4                    | Clamping range, max.  | 2.5 mm <sup>2</sup>  |
| Clamping range, min.  | 0.34 mm <sup>2</sup> | Blade size  | 0.6 x 3.5 mm         |
| Wire connection cross section AWG, min.   | AWG 22               | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup>  |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.34 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup>  |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.34 mm <sup>2</sup> | Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>    |
| Wire connection cross section, finely stranded, min.                                    | 0.34 mm <sup>2</sup> | Connection cross-section, stranded, max.  | 2.5 mm <sup>2</sup>  |
| Connection cross-section, stranded, min.  | 0.34 mm <sup>2</sup> | Wire connection cross-section, solid core, max.   | 2.5 mm <sup>2</sup>  |
| Wire connection cross-section, solid core, min.   | 0.34 mm <sup>2</sup> | Connection cross-section, finely stranded, min.   | 0.34 mm <sup>2</sup> |

### General

|   |                  |   |        |
|---|------------------|---|--------|
| Wire connection cross section AWG, max. | AWG 14           | Wire connection cross section AWG, min. | AWG 22 |
| Standards                               | DIN EN 60947-7-1 | Mounting rail                           | TS 35  |

### Rating data


|  |                     |                                 |                  |
|--|---------------------|---------------------------------|------------------|
| Rated cross-section                          | 2.5 mm <sup>2</sup> | Rated voltage                   | 500 V            |
| Rated DC voltage                             | 500 V               | Nominal current                 | 20 A             |
| Current at maximum wires                     | 20 A                | Standards                       | DIN EN 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ             | Rated impulse withstand voltage | 6 kV             |
| Power loss in accordance with IEC 60947-7-x  | 0.77 mW             | Surge voltage category          | III              |
| Pollution severity                           | 3                   |                                 |                  |

### UL rating data

|                                 |        |                         |        |
|---------------------------------|--------|-------------------------|--------|
| Voltage size B (cURus)          | 300 V  | Voltage size D (cURus)  | 600 V  |
| Wire cross section max. (cURus) | 12 AWG | Certificate No. (cURus) | E60693 |
| Wire cross section min. (cURus) | 22 AWG | Current size B (cURus)  | 20 A   |
| Voltage size C (cURus)          | 300 V  | Current size C (cURus)  | 20 A   |
| Current size D (cURus)          | 5 A    |                         |        |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000902    | ETIM 9.0    | EC000902    |
| ETIM 10.0   | EC000902    | ECLASS 14.0 | 27-25-01-09 |
| ECLASS 15.0 | 27-25-01-09 |             |             |



## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Component plugs



The component plug is used to integrate an electrical component in a disconnect terminal block. After soldering the electronic component, the plug can be integrated into the disconnection area of our disconnect terminal blocks and thus changes the disconnect terminal block into a modular terminal block with integrated electronic component.

## General ordering data

|            |                           |                                   |
|------------|---------------------------|-----------------------------------|
| Type       | BEST                      | Version                           |
| Order No.  | <a href="#">183310000</a> | Accessories, Component plug       |
| GTIN (EAN) | 4032248501014             |                                   |
| Qty.       | 50 ST                     |                                   |
| Type       | BEST/D                    | Version                           |
| Order No.  | <a href="#">187856000</a> | Accessories, Component plug, 1 A  |
| GTIN (EAN) | 4032248471492             |                                   |
| Qty.       | 50 ST                     |                                   |
| Type       | BEST/DRBR                 | Version                           |
| Order No.  | <a href="#">187857000</a> | Accessories, Component plug, 22 A |
| GTIN (EAN) | 4032248471508             |                                   |
| Qty.       | 50 ST                     |                                   |

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                           |   |
|------------|---------------------------|---|
| Type       | ZQV 2.5N/10               | Version   |
| Order No.  | <a href="#">152769000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm |
| GTIN (EAN) | 4050118447989             |   |
| Qty.       | 20 ST                     |   |
| Type       | ZQV 2.5N/10 BK            | Version   |
| Order No.  | <a href="#">283175000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm  |
| GTIN (EAN) | 4064675416982             |   |
| Qty.       | 20 ST                     |   |
| Type       | ZQV 2.5N/10 BL            | Version   |
| Order No.  | <a href="#">152788000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm   |
| GTIN (EAN) | 4050118448573             |   |
| Qty.       | 20 ST                     |   |

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZQV 2.5N/10 RD             | Version   |
| Order No.  | <a href="#">2108910000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 10,  |
| GTIN (EAN) | 4050118486018              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/10 WT             | Version   |
| Order No.  | <a href="#">2831640000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles:    |
| GTIN (EAN) | 4064675416876              | 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm             |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/2                 | Version   |
| Order No.  | <a href="#">1527540000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448467              | 2, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm               |
| Qty.       | 60 ST                      |   |
| Type       | 3360                       | Version   |
| Order No.  | <a href="#">2831670000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 2, |
| GTIN (EAN) | 4064675416906              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                  |
| Qty.       | 60 ST                      |   |
| Type       | ZQV 2.5N/2 BL              | Version   |
| Order No.  | <a href="#">1527740000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 2,  |
| GTIN (EAN) | 4050118448658              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                  |
| Qty.       | 60 ST                      |   |
| Type       | ZQV 2.5N/2 RD              | Version   |
| Order No.  | <a href="#">2108470000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 2,   |
| GTIN (EAN) | 4050118448542              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                  |
| Qty.       | 60 ST                      |   |
| Type       | ZQV 2.5N/2 WT              | Version   |
| Order No.  | <a href="#">2831560000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles: 2, |
| GTIN (EAN) | 4064675416692              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                  |
| Qty.       | 60 ST                      |   |
| Type       | ZQV 2.5N/20                | Version   |
| Order No.  | <a href="#">1527720000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118447972              | 20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm              |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/20 BK             | Version   |
| Order No.  | <a href="#">2831760000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles:    |
| GTIN (EAN) | 4064675416999              | 20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm              |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/20 BL             | Version   |
| Order No.  | <a href="#">1527890000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 20, |
| GTIN (EAN) | 4050118448566              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm                  |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/20 RD             | Version   |
| Order No.  | <a href="#">2108920000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 20,  |
| GTIN (EAN) | 4050118485899              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm                  |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/20 WT             | Version   |
| Order No.  | <a href="#">2831650000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles:    |
| GTIN (EAN) | 4064675416883              | 20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm              |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/3                 | Version   |
| Order No.  | <a href="#">1527570000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448450              | 3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                |
| Qty.       | 60 ST                      |   |

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |  |
|------------|----------------------------|--|
| Type       | ZQV 2.5N/3 BK              | Version  |
| Order No.  | <a href="#">2831680000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 3,  |
| GTIN (EAN) | 4064675416913              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                    |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5N/3 BL              | Version  |
| Order No.  | <a href="#">1527770000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 3,   |
| GTIN (EAN) | 4050118448641              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                    |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5N/3 RD              | Version  |
| Order No.  | <a href="#">2108690000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 3,    |
| GTIN (EAN) | 4050118448535              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                    |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5N/3 WT              | Version  |
| Order No.  | <a href="#">2831570000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles: 3,  |
| GTIN (EAN) | 4064675416807              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                    |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5N/4                 | Version  |
| Order No.  | <a href="#">1527590000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: 4, |
| GTIN (EAN) | 4050118448443              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5N/4 BK              | Version  |
| Order No.  | <a href="#">2831690000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 4,  |
| GTIN (EAN) | 4064675416920              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5N/4 BL              | Version  |
| Order No.  | <a href="#">1527780000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 4,   |
| GTIN (EAN) | 4050118448634              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5N/4 RD              | Version  |
| Order No.  | <a href="#">2108700000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 4,    |
| GTIN (EAN) | 4050118448528              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5N/4 WT              | Version  |
| Order No.  | <a href="#">2831580000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles: 4,  |
| GTIN (EAN) | 4064675416814              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                  |
| Qty.       | 60 ST                      |  |
| Type       | ZQV 2.5N/5                 | Version  |
| Order No.  | <a href="#">1527620000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: 5, |
| GTIN (EAN) | 4050118448436              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5N/5 BK              | Version  |
| Order No.  | <a href="#">2831700000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 5,  |
| GTIN (EAN) | 4064675416937              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5N/5 BL              | Version  |
| Order No.  | <a href="#">1527790000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 5,   |
| GTIN (EAN) | 4050118448627              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                  |
| Qty.       | 20 ST                      |  |
| Type       | ZQV 2.5N/5 RD              | Version  |
| Order No.  | <a href="#">2108710000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 5,    |
| GTIN (EAN) | 4050118448511              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                  |
| Qty.       | 20 ST                      |  |

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZQV 2.5N/5 WT              | Version   |
| Order No.  | <a href="#">2831590000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles: 5, |
| GTIN (EAN) | 4064675416821              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/50                | Version   |
| Order No.  | <a href="#">1527730000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118411362              | 50, Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm              |
| Qty.       | 5 ST                       |   |
| Type       | ZQV 2.5N/50 BK             | Version   |
| Order No.  | <a href="#">2831770000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles:    |
| GTIN (EAN) | 4064675417002              | 50, Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm              |
| Qty.       | 5 ST                       |   |
| Type       | ZQV 2.5N/50 BL             | Version   |
| Order No.  | <a href="#">1527920000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 50, |
| GTIN (EAN) | 4050118448559              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm                  |
| Qty.       | 5 ST                       |   |
| Type       | ZQV 2.5N/50 RD             | Version   |
| Order No.  | <a href="#">2109000000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 50,  |
| GTIN (EAN) | 4050118486001              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm                  |
| Qty.       | 5 ST                       |   |
| Type       | ZQV 2.5N/50 WT             | Version   |
| Order No.  | <a href="#">2831660000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles:    |
| GTIN (EAN) | 4064675416890              | 50, Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm              |
| Qty.       | 5 ST                       |   |
| Type       | ZQV 2.5N/6                 | Version   |
| Order No.  | <a href="#">1527630000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448429              | 6, Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm              |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/6 BK              | Version   |
| Order No.  | <a href="#">2831710000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 6, |
| GTIN (EAN) | 4064675416944              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/6 BL              | Version   |
| Order No.  | <a href="#">1527820000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 6,  |
| GTIN (EAN) | 4050118448610              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/6 RD              | Version   |
| Order No.  | <a href="#">2108720000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 6,   |
| GTIN (EAN) | 4050118448504              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/6 WT              | Version   |
| Order No.  | <a href="#">2831600000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles: 6, |
| GTIN (EAN) | 4064675416838              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/7                 | Version   |
| Order No.  | <a href="#">1527640000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448412              | 7, Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm              |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/7 BK              | Version   |
| Order No.  | <a href="#">2831720000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 7, |
| GTIN (EAN) | 4064675416951              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                 |
| Qty.       | 20 ST                      |   |

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZQV 2.5N/7 BL              | Version   |
| Order No.  | <a href="#">1527830000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 7,  |
| GTIN (EAN) | 4050118448603              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/7 RD              | Version   |
| Order No.  | <a href="#">2108810000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 7,   |
| GTIN (EAN) | 4050118448498              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/7 WT              | Version   |
| Order No.  | <a href="#">2831610000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles: 7, |
| GTIN (EAN) | 4064675416845              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/8                 | Version   |
| Order No.  | <a href="#">1527670000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448405              | 8, Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm              |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/8 BK              | Version   |
| Order No.  | <a href="#">2831730000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 8, |
| GTIN (EAN) | 4064675416968              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/8 BL              | Version   |
| Order No.  | <a href="#">1527840000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 8,  |
| GTIN (EAN) | 4050118448597              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/8 RD              | Version   |
| Order No.  | <a href="#">2108870000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 8,   |
| GTIN (EAN) | 4050118448481              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/8 WT              | Version   |
| Order No.  | <a href="#">2831620000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles: 8, |
| GTIN (EAN) | 4064675416852              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/9                 | Version   |
| Order No.  | <a href="#">1527680000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118447996              | 9, Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm              |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/9 BK              | Version   |
| Order No.  | <a href="#">2831740000</a> | Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 9, |
| GTIN (EAN) | 4064675416975              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/9 RD              | Version   |
| Order No.  | <a href="#">2108900000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 9,   |
| GTIN (EAN) | 4050118448474              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm                 |
| Qty.       | 20 ST                      |   |
| Type       | ZQV 2.5N/9 WT              | Version   |
| Order No.  | <a href="#">2831630000</a> | Cross-connector (terminal), Plugged, white, 24 A, Number of poles: 9, |
| GTIN (EAN) | 4064675416869              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm                 |
| Qty.       | 20 ST                      |   |

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

|            |                            |                       |
|------------|----------------------------|-----------------------|
| Type       | AEB 35 SC/1                | Version               |
| Order No.  | <a href="#">1991920000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118376722              |                       |
| Qty.       | 50 ST                      |                       |
| Type       | AEB 35 SC/1 BK             | Version               |
| Order No.  | <a href="#">2475310000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118487114              |                       |
| Qty.       | 50 ST                      |                       |
| Type       | AEB 35 SC/1 RM             | Version               |
| Order No.  | <a href="#">3112300000</a> | A-series, End bracket |
| GTIN (EAN) | 4099987196413              |                       |
| Qty.       | 50 ST                      |                       |
| Type       | AEB 35 SCL/1 RM            | Version               |
| Order No.  | <a href="#">3112310000</a> | A-series, End bracket |
| GTIN (EAN) | 4099987196420              |                       |
| Qty.       | 20 ST                      |                       |
| Type       | AEB 35 SCL/1 V0            | Version               |
| Order No.  | <a href="#">2661280000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702163              |                       |
| Qty.       | 20 ST                      |                       |
| Type       | AEB 35 SCL/1 V0 BK         | Version               |
| Order No.  | <a href="#">2661300000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702187              |                       |
| Qty.       | 20 ST                      |                       |
| Type       | AEB 35 SCL/1 V0 GY         | Version               |
| Order No.  | <a href="#">2661290000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702170              |                       |
| Qty.       | 20 ST                      |                       |

## Fuse holder



The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SIHA 3/G20                 | Version  |
| Order No.  | <a href="#">7926190000</a> | Fuse holder for feed-through modular terminal, black, 6.3 A,           |
| GTIN (EAN) | 4032248264612              | pluggable, V-0, Wemid  |
| Qty.       | 1000 ST                    |  |
| Type       | SIHA 3/G20                 | Version  |
| Order No.  | <a href="#">7921560000</a> | Fuse holder for feed-through modular terminal, black, 6.3 A,           |
| GTIN (EAN) | 4032248264643              | pluggable, V-0, Wemid  |
| Qty.       | 25 ST                      |  |
| Type       | SIHA 3/G20 BL              | Version  |
| Order No.  | <a href="#">1004260000</a> | Fuse holder for feed-through modular terminal, blue, 6.3 A, pluggable, |
| GTIN (EAN) | 4032248709717              | V-0, Wemid   |
| Qty.       | 25 ST                      |  |
| Type       | SIHA 3/G20/LD 10-36V       | Version  |
| Order No.  | <a href="#">7921570000</a> | Fuse holder for feed-through modular terminal, black, 2.31 mA,         |
| GTIN (EAN) | 4032248322503              | pluggable, V-0, Wemid  |
| Qty.       | 25 ST                      |  |
| Type       | SIHA 3/G20/LD 10-36V BL    | Version  |
| Order No.  | <a href="#">1005250000</a> | Fuse holder for feed-through modular terminal, blue, 2.31 A,           |
| GTIN (EAN) | 4032248712038              | pluggable, V-0, Wemid  |
| Qty.       | 25 ST                      |  |
| Type       | SIHA 3/G20/LD 140-250V     | Version  |
| Order No.  | <a href="#">7921600000</a> | Fuse holder for feed-through modular terminal, black, 2.31 mA,         |
| GTIN (EAN) | 4032248322633              | pluggable, V-0, Wemid  |
| Qty.       | 25 ST                      |  |
| Type       | SIHA 3/G20/LD 35-70V       | Version  |
| Order No.  | <a href="#">7921580000</a> | Fuse holder for feed-through modular terminal, black, 2.31 mA,         |
| GTIN (EAN) | 4032248322619              | pluggable, V-0, Wemid  |
| Qty.       | 25 ST                      |  |
| Type       | SIHA 3/G20/LD 60-150V      | Version  |
| Order No.  | <a href="#">7921590000</a> | Fuse holder for feed-through modular terminal, black, 2.31 mA,         |
| GTIN (EAN) | 4032248322626              | pluggable, V-0, Wemid  |
| Qty.       | 25 ST                      |  |

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/5 MC NE BL           | Version   |
| Order No.  | <a href="#">1609801693</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397166              | Weidmueller, blue   |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 MC NE BR           | Version   |
| Order No.  | <a href="#">1249870000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118051865              | Weidmueller, brown  |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 MC NE GE           | Version   |
| Order No.  | <a href="#">1609801687</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397135              | Weidmueller, yellow                                       |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 MC NE GN           | Version   |
| Order No.  | <a href="#">1609801688</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397142              | Weidmueller, green  |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 MC NE GR           | Version   |
| Order No.  | <a href="#">1609801691</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397159              | Weidmueller, grey   |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 MC NE RT           | Version   |
| Order No.  | <a href="#">1609801686</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397128              | Weidmueller, red  |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 MC NE OR           | Version   |
| Order No.  | <a href="#">1238340000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118062632              | Weidmueller, orange                                       |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 MC NE SW           | Version   |
| Order No.  | <a href="#">1457550000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118263817              | Weidmueller, black  |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 MC NE VI           | Version   |
| Order No.  | <a href="#">1249860000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118042764              | Weidmueller, violet                                       |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 MC NE WS           | Version   |
| Order No.  | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111              | Weidmueller, white  |
| Qty.       | 1000 ST                    |   |
| Type       | DEK 5/5 S MC NE WS         | Version   |
| Order No.  | <a href="#">1341620000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118145793              | Weidmueller, white  |
| Qty.       | 400 ST                     |   |

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/5 MC SDR             | Version   |
| Order No.  | <a href="#">1609810000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190456597              | Weidmueller, To customer specification                    |
| Qty.       | 200 ST                     |   |
| Type       | DEK 5/5 PLUS MC SDR        | Version   |
| Order No.  | <a href="#">1854500000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4032248393602              | Weidmueller, To customer specification                    |
| Qty.       | 200 ST                     |   |
| Type       | DEK 5/5 S MC SDR           | Version   |
| Order No.  | <a href="#">1341590000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118146042              | Weidmueller, To customer specification                    |
| Qty.       | 80 ST                      |   |

## Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
  - Markers in proven MultiCard format
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | WS 8/5 MC NE BL            | Version   |
| Order No.  | <a href="#">1773521693</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141715              | Allen-Bradley, blue   |
| Qty.       | 720 ST                     |   |

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | WS 8/5 MC NE GE            | Version   |
| Order No.  | <a href="#">1773521687</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141548              | Allen-Bradley, yellow   |
| Qty.       | 720 ST                     |   |
| Type       | WS 8/5 MC NE OR            | Version   |
| Order No.  | <a href="#">1773521690</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248143092              | Allen-Bradley, orange   |
| Qty.       | 720 ST                     |   |
| Type       | WS 8/5 MC NE RT            | Version   |
| Order No.  | <a href="#">1773521686</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141531              | Allen-Bradley, red  |
| Qty.       | 720 ST                     |   |
| Type       | WS 8/5 MC NE WS            | Version   |
| Order No.  | <a href="#">1640740000</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190279103              | Allen-Bradley, white  |
| Qty.       | 720 ST                     |   |
| Type       | WS 8/5 PLUS MC NE WS       | Version   |
| Order No.  | <a href="#">1951870000</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248631605              | Allen-Bradley, white  |
| Qty.       | 600 ST                     |   |

## DEK 5/5



### WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

### General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | DEK 5/5 MM BP WS           | Version  |
| Order No.  | <a href="#">2619770000</a> | Dekafix, Terminal marker, 5 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118626315              |  |
| Qty.       | 10000 ST                   |  |
| Type       | DEK 5/5 MM WS              | Version  |
| Order No.  | <a href="#">2007110000</a> | Dekafix, Terminal marker, 5 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118391862              |  |
| Qty.       | 800 ST                     |  |

## SDT 2.5 4C BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## WS 8/5



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | WS 8/5 MM BP WS            | Version   |  |
| Order No.  | <a href="#">2619810000</a> | WS, Terminal marker, 8 x 5 mm, Weidmueller, white |  |
| GTIN (EAN) | 4050118626278              |   |  |
| Qty.       | 8000 ST                    |   |  |
| Type       | WS 8/5 MM WS               | Version   |  |
| Order No.  | <a href="#">2007150000</a> | WS, Terminal marker, 8 x 5 mm, Weidmueller, white |  |
| GTIN (EAN) | 4050118392029              |   |  |
| Qty.       | 800 ST                     |   |  |

## End plates and partition plates



Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

## General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | SEP DT 2.5 4C              | Version  |  |
| Order No.  | <a href="#">2929670000</a> | End plate for terminals, dark beige, Height: 95 mm, Width: 2.1 mm, |  |
| GTIN (EAN) | 4099986665279              | V-0, Wemid, Snap-on: Yes   |  |
| Qty.       | 50 ST                      |  |  |

## SDT 2.5 4C BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Disconnect plugs



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

### General ordering data

|            |                            |                       |  |
|------------|----------------------------|-----------------------|--|
| Type       | AFTC                       | Version               |  |
| Order No.  | <a href="#">2863420000</a> | Cover hood (terminal) |  |
| GTIN (EAN) | 40646755965 16             |                       |  |
| Qty.       | 50 ST                      |                       |  |

### Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

### General ordering data

|            |                            |  |  |
|------------|----------------------------|--|--|
| Type       | FZS 2/4 RT/80 SAKT4        | Version  |  |
| Order No.  | <a href="#">1276300000</a> | Plug (terminal), Plug-in connection, 2 mm <sup>2</sup> , Number of connections: 2, |  |
| GTIN (EAN) | 4008190026080              | Number of poles: 1, Width: 9 mm  |  |
| Qty.       | 20 ST                      |  |  |