

## AC SB M 32A 4POL CG 06KV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Photovoltaics, Switch, Switch disconnecter, 600 V AC, 32 A, 4 pole, Manual switch
Order No.	<a href="#">3103140000</a>
Type	AC SB M 32A 4POL CG 06KV
GTIN (EAN)	4099987148344
Qty.	1 items

## AC SB M 32A 4POL CG 06KV

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	121.1 mm	Depth (inches)	4.7677 inch
Height	165 mm	Height (inches)	6.4961 inch
Width	140 mm	Width (inches)	5.5118 inch
Net weight	526 g		

### Temperatures

Ambient temperature -25 °C...55 °C

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

### Guarantee

Time interval 5 years

### General data

Standards IEC 60947-3 Protection degree IP65  
 Installation location Protected outdoor area (>1 km from sea)

### Load break switch

Voltage type	AC	Nominal voltage	800 V
Nominal current	32 A	Number of contacts as NC contact	0
Rated mainly active load-breaking current	32 A	Connection type	Screw tension clamp 1,5 - 10 mm <sup>2</sup>
Short Circuit Interrupt Capability	10 kA	Rated short-circuit making current	400 A
Rated peak withstand current	10 kA	Number of breaking operation cycles at rated current	1500
Mechanical endurance class	M2 (10000)	Rated take-over current	200 A
Number of contacts as NO contact	4		

### Connection

Design as main switch Yes Device with pre-assembled cabling No

### Classifications

ETIM 8.0	EC000216	ETIM 9.0	EC000216
ETIM 10.0	EC000216	ECLASS 14.0	27-37-14-03
ECLASS 15.0	27-37-14-03		

## AC SB M 32A 4POL CG 06KV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Technical data

[www.weidmueller.com](http://www.weidmueller.com)

### Tender specification sheets

Long specification	<p>Load break Switch in polyester housing. Suitable for disconnection on the AC side. Number of poles: 4 Rated operational current (I<sub>e</sub>) (I<sub>e</sub>): - according to IEC (AC-21): 32 A Rated operational voltage (U<sub>e</sub>): - according to IEC: 690 V Suitability for use: Emergency Stop Switch: Yes Main Switch: Yes Number of contacts normally open: 4 Number of contacts normally closed: 0 Number of switching positions: 2 Lockable: Yes The switch is mounted using 4 screws. Protection class (IP): 65 Polyester housing with knockouts for cable glands PG 16/21. Dimensions HxWxD: 165x140x121 mm. Approved according to Low-voltage Switchgear and Controlgear: IEC 60947-3, DIN VDE 0660 Part 107 (EN 60947-3)</p>
--------------------	---

AC SB M 32A 4POL CG 06KV

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

