

AC SB M 100A 4POL CG 06KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Photovoltaics, Switch, Switch disconnecter, 600 V AC, 100 A, 4 pole, Manual switch
Order No.	3103170000
Type	AC SB M 100A 4POL CG 06KV
GTIN (EAN)	4099987148375
Qty.	1 items

AC SB M 100A 4POL CG 06KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	121.1 mm	Depth (inches)	4.7677 inch
Height	165 mm	Height (inches)	6.4961 inch
Width	140 mm	Width (inches)	5.5118 inch
Net weight	773 g		

Temperatures

Ambient temperature -25 °C...50 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Guarantee

Time interval 5 years

General data

Standards	IEC 60947-3	Protection degree	IP66, IP65
Installation location	Protected outdoor area (>1 km from sea)		

Load break switch

Voltage type	AC	Nominal voltage	690 V
Nominal current	100 A	Number of contacts as NC contact	0
Rated mainly active load-breaking current	100 A	Connection type	Screw tension clamp 6 - 35 mm ²
Short Circuit Interrupt Capability	15 kA	Rated short-circuit making current	1500 A
Rated peak withstand current	1500 A	Number of breaking operation cycles at rated current	1500
Mechanical endurance class	M2 (10000)	Rated take-over current	600 A
Number of contacts as NO contact	4		

Connection

Design as main switch	Yes	Device with pre-assembled cabling	No
-----------------------	-----	-----------------------------------	----

Classifications

ETIM 8.0	EC000216	ETIM 9.0	EC000216
ETIM 10.0	EC000216	ECLASS 14.0	27-37-14-03
ECLASS 15.0	27-37-14-03		

AC SB M 100A 4POL CG 06KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Technical data

www.weidmueller.com

Tender specification sheets

Long specification	<p>Load break Switch in polyester housing. Suitable for disconnection on the AC side. Number of poles: 4 Rated operational current (Ie) (Ie): - according to IEC (AC-21): 100 A Rated operational voltage (Ue): - according to IEC: 690 V Suitability for use: Emergency Stop Switch: Yes Main Switch: Yes Number of contacts normally open: 4 Number of contacts normally closed: 0 Number of switching positions: 2 Lockable: Yes The switch is mounted using 4 screws. Protection class (IP): 65 Polyester housing with knockouts for cable glands PG 16/21. Dimensions HxWxD: 165x140x121 mm. Approved according to Low-voltage Switchgear and Controlgear: IEC 60947-3, DIN VDE 0660 Part 107 (EN 60947-3)</p>
--------------------	---

