

HDC 16B ABU BP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Plastic enclosures are particularly suitable for applications where the resistance of metals is not sufficient. In addition, the enclosures shown here are lighter and slightly cheaper than standard aluminum enclosures. It can therefore make sense to use plastic enclosures in applications where the materials do not need to be as robust. The tightness is still IP65.

General ordering data

| | |
|------------|--|
| Version | HDC enclosures, Installation size: 6, Protection degree: IP65, in plugged condition, Bulkhead housing, Side-locking clamp on lower side, Side-locking clamp not replaceable, Standard, Size of cable entries: none |
| Order No. | 3107150000 |
| Type | HDC 16B ABU BP |
| GTIN (EAN) | 4099987172028 |
| Qty. | 1 items |

HDC 16B ABU BP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 43 mm | Depth (inches) | 1.6929 inch |
| Height | 30.6 mm | Height (inches) | 1.2047 inch |
| Width | 113 mm | Width (inches) | 4.4488 inch |
| Length | 113 mm | Length (inches) | 4.4488 inch |
| Net weight | 99 g | | |

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Dimensions

Cable entry No

General data

UL 94 flammability rating V-0 Protection degree IP65, in plugged condition

Version

| | | | |
|-----------------------|--------------------|--------------------------------|--|
| Size of cable entries | none | Top part/bottom part/lid | lower part |
| Cover | without cover | Number of cable entry sideways | 0 |
| Design of housing | Bulkhead housing | Design of locking system | Side-locking clamp on lower side, Side-locking clamp not replaceable |
| Design | Standard | Installation size | 6 |
| Cable entry | No | Type | Bulkhead (feed-through) |
| Clamp version | Side-locking clamp | Sealing | NBR |
| Internal thread | M 32 | Colour (RAL) | RAL 9005 |
| BG | 6 | Suitable for ModuPlug® | Yes |

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ETIM 10.0 | EC000437 | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 | | |

HDC 16B ABU BP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC 16B ABU BP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Hood, Cable Entry sideways



Plastic enclosures are particularly suitable for applications where the resistance of metals is not sufficient. In addition, the enclosures shown here are lighter and slightly cheaper than standard aluminum enclosures. It can therefore make sense to use plastic enclosures in applications where the materials do not need to be as robust. The tightness is still IP65.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | HDC 40D TSBU 1M32 BP | Version | |
| Order No. | 3107200000 | HDC enclosures, Installation size: 6, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32, M 40 | |
| GTIN (EAN) | 4099987 172 127 | | |
| Qty. | 1 ST | | |

Hood, Cable Entry at top



Plastic enclosures are particularly suitable for applications where the resistance of metals is not sufficient. In addition, the enclosures shown here are lighter and slightly cheaper than standard aluminum enclosures. It can therefore make sense to use plastic enclosures in applications where the materials do not need to be as robust. The tightness is still IP65.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | HDC 40D TOBU 1M32 BP | Version | |
| Order No. | 3164310000 | HDC enclosures, Installation size: 6, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32, M 40 | |
| GTIN (EAN) | 4099987800181 | | |
| Qty. | 1 ST | | |

Size 4



The PUSH IN connection is a direct-insert method of connection. The preprocessed wire can be inserted directly into the wire connection without the need for any tools.

Number of poles: 10

Rated current: 16 A

Rated voltage: 500 V

Nominal voltage acc. to UL/CSA: 600 V AC/DC

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | HDC HE 10 FP | Version | |
| Order No. | 1873540000 | HDC insert, Female, 500 V, 16 A, Number of poles: 10, PUSH IN, Installation size: 4 | |
| GTIN (EAN) | 4032248458158 | | |
| Qty. | 1 ST | | |

HDC 16B ABU BP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | HDC HE 10 MP | Version |
| Order No. | 1873550000 | HDC insert, Male, 500 V, 16 A, Number of poles: 10, PUSH IN, |
| GTIN (EAN) | 4032248458165 | Installation size: 4 |
| Qty. | 1 ST | |