

**HDMI A S1V 1.9N1 RL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



HDMI sockets for PCBs - reliable connectivity for your electronics projects

HDMI sockets from Weidmüller offer a high-quality solution for the transmission of video, audio and Ethernet signals (HEC) in industrial applications

Features and benefits:

- Compact design: Ideal for space-saving PCB designs thanks to various outlet directions
- High data transmission rate: Supports HDMI 2.0 and 4K resolutions and Ethernet up to 100 Mbit/s
- Easy integration: Standardized design facilitates mounting and integration into the device
- EMC protection: Reliable protection against interference for clean data transmission
- Perfectly suited for processing in automated SMT processes thanks to tape-on-reel packaging
- Durability: Robust design ensures a reliability in demanding environments

**General ordering data**

Version	, female header, 100 MBit/s, SMD solder connection, 180°, Plugging cycles: ≥ 10000, Number of poles: 5, LCP, Gold over nickel, Tape
Order No.	<a href="#">3107660000</a>
Type	HDMI A S1V 1.9N1 RL
GTIN (EAN)	4099987174633
Qty.	1600 items
Packaging	Tape

## HDMI A S1V 1.9N1 RL

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	6.2 mm	Depth (inches)	0.2441 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	0.01 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## System specifications

Number of poles	5	LED	No
Mounting onto the PCB	SMD solder connection	Pitch in inches (P)	0.020 "
Shielding material	Stainless steel	Shielding	Yes, 360° shield contact
Plugging force/pole, max.	35 N	Transmission rate	100 MBit/s
Number of solder pins per pole	1	Type of connection	Socket connector
Pitch in mm (P)	0.50 mm	Protection degree	IP20
Plugging cycles	≥ 10000	Model	Socket connector
Outgoing elbow	180°	Shield surface	nickel-plated
Performance-Category	100 MBit/s	Soldering process	Reflow soldering, Manual soldering
Pulling force / pole, min.	10.00 N	Solder pin dimensions	Octagonal

## Electrical properties

Dielectric strength, contact / contact	500 V AC / 1 min	Volume resistance	≤10 mΩ
Insulation resistance	≥ 100 MΩ		

## Material data

Insulating material	LCP	Colour	black
Colour chart (similar)	RAL 9011	Insulation resistance	≥ 100 MΩ
Moisture Level (MSL)	1	UL 94 flammability rating	V-0
Contact base material	Copper alloy	Contact material	Cu-alloy
Contact surface	Gold over nickel	Layer structure of plug contact	≤ 1 μ" Au
Storage temperature, min.	-20 °C	Storage temperature, max.	65 °C
Operating temperature, min.	-20 °C	Operating temperature, max.	65 °C

## Packing

Packaging	Tape	VPE length	0.00 mm
VPE width	0.00 mm	VPE height	0.00 mm

## Important note

Notes

**HDMI A S1V 1.9N1 RL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Classifications**

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		

**Drawings**



**HDMI A S1V 1.9N1 RL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

**Drawings**

www.weidmueller.com

