



## SLF 5.08/10/180DF SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Product image



Similar to illustration

Male plug with PUSH IN wire connection and straight outlet direction, when used with BLF 5.08HC as wire-to-wire application for panel feed-through. The male plugs provide space for labelling and can be coded.

### General ordering data

|              |   |
|--------------|---|
| Version      | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 10, 180°, PUSH IN with actuator, Clamping range, max. : 3.31 mm², Box |
| Order No.    | <a href="#">2989720000</a>  |
| Type         | SLF 5.08/10/180DF SN BK BX  |
| GTIN (EAN)   | 4099986860995   |
| Qty.         | 24 items  |
| Product data | IEC: 400 V / 25.9 A / 0.2 - 2.5 mm²<br>UL: 300 V / 14 A / AWG 26 - AWG 12   |
| Packaging    | Box   |

## SLF 5.08/10/180DF SN BK BX

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform  
UL File Number Search [UL Website](#)  
Certificate No. (cURus) E60693

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 31 mm   | Depth (inches)  | 1.2205 inch |
| Height     | 14.2 mm | Height (inches) | 0.5591 inch |
| Net weight | 21.6 g  |                 |             |

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

## System Parameters

|                          |  |  |                              |
|--------------------------|--|--|------------------------------|
| Product family           | OMNIMATE Signal - series<br>BL/SL 5.08 | Type of connection                         | Field connection             |
| Wire connection method   | PUSH IN with actuator                  | Pitch in mm (P)                            | 5.08 mm                      |
| Pitch in inches (P)      | 0.200 "                                | Conductor outlet direction                 | 180°                         |
| Number of poles          | 10                                     | L1 in mm                                   | 45.72 mm                     |
| L1 in inches             | 1.800 "                                | Pin series quantity                        | 1                            |
| Rated cross-section      | 2.5 mm <sup>2</sup>                    | Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged/ IP10 unplugged |
| Protection degree        | IP20                                   | Volume resistance                          | 4.50 mΩ                      |
| Can be coded             | Yes                                    | Stripping length                           | 10 mm                        |
| Screwdriver blade        | 0.6 x 3.5                              | Screwdriver blade standard                 | DIN 5264                     |
| Plugging cycles          | 25                                     | Plugging force/pole, max.                  | 7 N                          |
| Pulling force/pole, max. | 5.5 N                                  |  |                              |

## Material data

|                                       |          |                                       |          |
|---------------------------------------|----------|---------------------------------------|----------|
| Insulating material                   | PBT      | Colour                                | black    |
| Colour of operational elements        | orange   | Colour chart (similar)                | RAL 9011 |
| Moisture Level (MSL)                  |          | UL 94 flammability rating             | V-0      |
| Contact material                      | Cu-alloy | Contact surface                       | tinned   |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C    |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C   |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 100 °C   |

## Conductors suitable for connection

|   |                      |   |                      |
|---|----------------------|---|----------------------|
| Clamping range, min.  | 0.13 mm <sup>2</sup> | Clamping range, max.  | 3.31 mm <sup>2</sup> |
| Wire connection cross section AWG, min.                             | AWG 26               | Wire connection cross section AWG, max.                             | AWG 12               |
| Solid, min. H05(07) V-U   | 0.2 mm <sup>2</sup>  | Solid, max. H05(07) V-U   | 2.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K  | 0.2 mm <sup>2</sup>  | Flexible, max. H05(07) V-K  | 2.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                      | w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm <sup>2</sup> max. |                      |
| w. wire end ferrule, DIN 46228 pt 1, min.                           | 0.2 mm <sup>2</sup>  | w. wire end ferrule, DIN 46228 pt 1, max.                           | 2.5 mm <sup>2</sup>  |

## SLF 5.08/10/180DF SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Technical data

|   |                 |                |  |
|---|-----------------|----------------|--|
| Plug gauge in accordance with EN 60999 a x b; ø | 2.8 mm x 2.0 mm | Reference text | The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage. |
|---|-----------------|----------------|--|

#### Rated data acc. to IEC

|   |                        |   |                   |
|---|------------------------|---|-------------------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 25.9 A            |
| Rated current, max. number of poles (Tu=20°C)                             | 21.7 A                 | Rated current, min. number of poles (Tu=40°C)                         | 22.5 A            |
| Rated current, max. number of poles (Tu=40°C)                             | 18.5 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4000 V                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

#### Rated data acc. to CSA

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 10 A   | Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, min.     | AWG 26 | Wire cross-section, AWG, max.     | AWG 12 |

#### Rated data acc. to UL 1059

|                                       |  |                                       |        |
|---------------------------------------|--|---------------------------------------|--------|
| Institute (cURus)                     | CURUS  | Certificate No. (cURus)               | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 14 A   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 26   | Wire cross-section, AWG, max.         | AWG 12 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

#### Packing

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 354.00 mm |
| VPE width | 143.00 mm | VPE height | 39.00 mm  |

#### Important note

IPC conformity  
 Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

- Notes
- Additional variants on request
  - Gold-plated contact surfaces on request
  - Rated current related to rated cross-section & min. No. of poles.
  - Wire end ferrule without plastic collar to DIN 46228/1
  - Wire end ferrule with plastic collar to DIN 46228/4
  - P on drawing = pitch
  - Crimping shape "A" for wire end ferrules with PZ 6/5 crimping tool recommended.
  - The test point can only be used as potential-pickup point.
  - In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load

## SLF 5.08/10/180DF SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002638    | ETIM 9.0    | EC002638    |
| ETIM 10.0   | EC002638    | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 |             |             |




**Drawings**

**Product benefits**



Lower assembly costs  
Secure in a matter of seconds

**Product benefits**



Easy handling  
No implementation framework necessary