

HDC 06B ALU EXI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The option of disconnecting cables in the EXI area simplifies installation and servicing and enables better preparation.

The Rockstar® EXI enclosures shown here are identified for use by their article designation.

A blue color is therefore not required. A blue EXI gland is required to complete the enclosure.

General ordering data

Version	HDC enclosures, Installation size: 3, Protection degree: IP65, in plugged condition, Bulkhead housing, End-locking clamp, lower side, End-locking clamp not replaceable, Standard
Order No.	3001300000
Type	HDC 06B ALU EXI
GTIN (EAN)	409998690238 1
Qty.	1 items

HDC 06B ALU EXI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	80 mm	Depth (inches)	3.1496 inch
Height	29 mm	Height (inches)	1.1417 inch
Width	45 mm	Width (inches)	1.7716 inch
Mounting dimension - height	32 mm	Mounting dimension - width	70 mm
Net weight	96.8 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	e98b2b24-ba23-41bf-8d19-0dda3647412f

Dimensions

Hole pitch length A2	70 mm	Cable entry	No
Width housing C	43 mm	Width base C1	47 mm
Total length housing	60 mm	Height of housing B	29 mm
Height of base B1	5.5 mm		

General data

UL 94 flammability rating	V-0	Surface finish	Powder coating
Protection degree	IP65, in plugged condition	Explosion protection type	II 2G Ex ib IIC T6 Gb

Version

Number of cable glands	0	Top part/bottom part/lid	lower part
Cover	without cover	Tightening torque	1.2 Nm
Number of cable entry sideways	0	Type of connection	PUSH IN
Design of housing	Bulkhead housing	Design of locking system	End-locking clamp, lower side, End-locking clamp not replaceable
Design	Standard	Installation size	3
Cable entry	No	Type	Bulkhead (feed-through)
Clamp version	End-locking clamp	Sealing	NBR
Colour (RAL)	RAL 7035	BG	3
Suitable for ModuPlug®	Yes		

Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC 06B ALU EXI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Chloroprene seal material, -40°C - +70°C




Polyamide cable glands, which are suitable for usage in explosion risk zones Ex e (increased safety) and Ex i (intrinsic safety). Weidmüller offers a product family without restrictions and besides compliance with standards, the cable gland excels thanks to its increased impact resistance of 4/7 Joule and a possible temperature range down to -60°C without restrictions. They have been tested to the current standard and EN 60079-0 directive, they are ATEX and IECEx certified.

General ordering data

Type	VG M20 EXI 7-13 CR7J G4	Version
Order No.	2722250000	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 20,
GTIN (EAN)	4050118821482	10 mm, OD min. 7 - OD max. 13 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	50 ST	(30 min.), Polyamide 6
Type	VG M20 EXI 11-14 CR7J G4	Version
Order No.	2722260000	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 20,
GTIN (EAN)	4050118821499	10 mm, OD min. 11 - OD max. 14 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	50 ST	(30 min.), Polyamide 6
Type	VG M20 EXI 7-12 CR7J G4	Version
Order No.	2722240000	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 20,
GTIN (EAN)	4050118821475	10 mm, OD min. 7 - OD max. 12 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	50 ST	(30 min.), Polyamide 6

Size 3



The ability to disconnect cables in the EXI area simplifies installation and service and enables better preparation. The Rockstar® EXI inserts shown here are equipped with PUSH IN connections and are therefore very easy to connect. They are identified by the article designation

General ordering data

Type	HDC HE 6 FP EXI	Version
Order No.	3001190000	, Female, 500 V, 5 A, Number of poles: 6, PUSH IN, Installation size: 3
GTIN (EAN)	4099986902305	
Qty.	1 ST	
Type	HDC HE 6 MP EXI	Version
Order No.	3001200000	, Male, 500 V, 5 A, Number of poles: 6, PUSH IN, Installation size: 3
GTIN (EAN)	4099986902312	
Qty.	1 ST	