

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Connecting sleeve (terminal), when screwed in, Width: 8 mm, Height: 8 mm, Depth: 28.1 mm, Number of poles: 1, Copper
Order No.	<a href="#">3011910000</a>
Type	VH 28.1/8/6.4
GTIN (EAN)	4099986918146
Qty.	5 items

**Technical data**

**Dimensions and weights**

Depth	28.1 mm	Depth (inches)	1.1063 inch
Height	8 mm	Height (inches)	0.315 inch
Width	8 mm	Width (inches)	0.315 inch
Diameter	8 mm	Net weight	4.45 g

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Copper	Colour	grey
UL 94 flammability rating	None		

**Additional technical data**

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

**Dimensions**

Diameter	8 mm
----------	------

**General**

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		