

CB-DT 365/7.5 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



With our detectable marking solutions, we support our food and beverage industry customers in ensuring the high standards required within the HACCP concept. Due to a metallic filler, our detectable Cable Ties are identified reliably by metal and X-ray detectors. Identification minimises the risk of contamination during the food production process. MultiCards provide maximal safety because of properties like corrosion resistance. We regularly check and confirm the safety properties in our accredited laboratory. Actual colour may vary, the tone does not affect the product characteristics. Not suitable for direct contact with food.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler

General ordering data

| | |
|------------|----------------------------------|
| Order No. | 3012740000 |
| Type | CB-DT 365/7.5 BL |
| GTIN (EAN) | 4099986921924 |
| Qty. | 100 items |

CB-DT 365/7.5 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|--------------|
| Depth | 1 mm | Depth (inches) | 0.0394 inch |
| Height | 365 mm | Height (inches) | 14.3701 inch |
| Width | 7.5 mm | Width (inches) | 0.2953 inch |
| Net weight | 1 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Installation materials

| | | | |
|-----------------------------------------|-----------|--------------------------------|---------|
| UV-resistant | No | For re-opening | No |
| UL 94 flammability rating | UL 94, HB | Halogen | No |
| Basic material | PA 6.6 | Tensile strength | 540 N |
| Bundle diameter, max. | 100 mm | Tensile strength (Pound-force) | 121 lbf |
| Detectible in accordance with Rondotest | 4.7 mm Al | Bundle diameter, min. | 8 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000046 | ETIM 9.0 | EC000046 |
| ETIM 10.0 | EC000046 | ECLASS 14.0 | 27-14-07-02 |
| ECLASS 15.0 | 27-14-07-02 | | |

Drawings

