

Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com



To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

General ordering data

Version	Feed-through terminal block, SNAP IN, grey, 2.5 mm², 24 A, 800 V, Number of connections: 2
Order No.	<u>3112230000</u>
Туре	S2C 2.5 GY
GTIN (EAN)	4099987196345
Qty.	100 items



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Aр	pr	OV	al	S
----	----	----	----	---

Approvals



UL File Number Search	<u>UL Website</u>
Certificate No. (cURus)	E60693
Certificate No. (cURusEX)	E184763

Dimensions and weights

Depth	38 mm	Depth (inches)	1.4961 inch
Height	59 mm	Height (inches)	2.3228 inch
Width	5.1 mm	Width (inches)	0.2008 inch
Net weight	8.45 g		

Temperatures

Storage temperature	-25 °C55 °C	Continuous operating temp., min.	-60 °C	
Continuous operating temp., max.	130 °C			

Material data

Basic material	Wemid	Colour	grey	
Colour of operational elements	green	UL 94 flammability rating	V-0	

System specifications

End cover plate required	Yes	Number of potentials	1
Number of levels	1	Number of clamping points per level	2
Number of potentials per tier	1	Levels cross-connected internally	No
Mounting rail	TS 35	N-function	No
PE function	No	PEN function	No

Additional technical data

Open sides	right	Snap-on	Yes	
Type of fixing	Snap-on	Explosion-tested version	No	
Type of mounting	Snap-on			

Conductors for clamping (additional connection)

Connection type, additional connection SNAP IN

Conductors for clamping (rated connection)

Gauge to IEC 60947-1	A2
Wire connection cross section AWG, max.	AWG 14
Connection direction	top
Stripping length	10 mm
Type of connection	SNAP IN
Number of connections	2
Clamping range, max.	2.5 mm ²
Clamping range, min.	0.34 mm ²
Blade size	0.6 x 3.5 mm

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Wire connection cross section AWG, min.	AWG 22	
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	2.5 mm ²	
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.34 mm ²	
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	2.5 mm ²	
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.34 mm ²	
Wire connection cross section, finely stranded, max.	4 mm ²	
Wire connection cross section, finely stranded, min.	0.34 mm ²	
Connection cross-section, stranded, max.	2.5 mm ²	
Connection cross-section, stranded, min	. 0.34 mm²	
Twin wire-end ferrules, max.	0.75 mm ²	
Twin wire-end ferrules, min.	0.5 mm ²	
Wire connection cross-section, solid	2.5 mm ²	
core, max.		
Wire connection cross-section, solid core, min.	0.34 mm ²	
Connection cross-section, finely stranded, min.	0.34 mm ²	
Tube length for wire-end ferrule with	Cross-section, min.	0.25 mm ²
plastic collar acc. to cross-section	Cross-section, max.	0.34 mm²
	Tube length, min.	8 mm
	Tube length, max.	8 mm
	Cross-section, min.	0.5 mm ²
	Cross-section, max.	1 mm ²
	Tube length, min.	8 mm
	Tube length, max.	12 mm
	Cross-section, min.	1.5 mm ²
	Cross-section, max.	2.5 mm ²
	Tube length, min.	10 mm
	Tube length, max.	18 mm
Tube length for wire-end ferrule without	Cross-section, min.	0.5 mm ²
plastic collar acc. to cross-section	Cross-section, max.	1 mm ²
	Tube length, min.	10 mm
	Tube length, max.	10 mm
	Cross-section, min.	1.5 mm ²
	Cross-section, max.	2.5 mm ²
	Tube length, min.	10 mm
	Tube length, max.	18 mm
Tube length for twin wire-end ferrule acc. to cross-section	Cross-section, min.	0.5 mm²
	Cross-section, max.	0.5 mm²
	Tube length, min.	8 mm
	Tubo longth may	12 mm
	Tube length, max.	
	Cross-section, min.	0.75 mm ²
	Cross-section, min.	0.75 mm ²





Weidmüller Interface GmbH & Co. KG

4

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

General

Wire connection cross section AWG,	AWG 14	Wire connection cross section AWG,	AWG 22
max.		min.	
Standards	IEC 60947-7-1	Mounting rail	TS 35

Rating data

Rated cross-section	2.5 mm ²	Rated voltage	800 V
Rated DC voltage	800 V	Nominal current	24 A
Current at maximum wires	24 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1.33 mΩ	Rated impulse withstand voltage	8 kV
Power loss in accordance with IEC 60947-7-x	0.77 mW	Surge voltage category	III
Pollution severity	3		

UL rating data

Conductor size Factory wiring max. (cURus)	12 AWG	Voltage size B (cURus)	600 V
Voltage size D (cURus)	600 V	Certificate No. (cURus)	E60693
Conductor size Field wiring min. (cUR	us) 22 AWG	Conductor size Factory wiring min. (cURus)	22 AWG
Current size B (cURus)	20 A	Voltage size C (cURus)	600 V
Current size C (cURus)	20 A	Current size D (cURus)	5 A
Conductor size Field wiring max. (cUR	us)12 AWG		

Classifications

EC000897	ETIM 7.0	EC000897
EC000897	ETIM 9.0	EC000897
EC000897	ECLASS 9.0	27-14-11-20
27-14-11-20	ECLASS 10.0	27-14-11-20
27-14-11-20	ECLASS 12.0	27-14-11-20
27-25-01-01	ECLASS 14.0	27-25-01-01
27-25-01-01		
	EC000897 EC000897 27-14-11-20 27-14-11-20 27-25-01-01	EC000897 ETIM 9.0 EC000897 ECLASS 9.0 27-14-11-20 ECLASS 10.0 27-14-11-20 ECLASS 12.0 27-25-01-01 ECLASS 14.0



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings









Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

End bracket









Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type Order No. GTIN (EAN) AEB 35 SC/1

1991920000 4050118376722

Qty. 50 ST

Version

A-series, End bracket

Testadapter and testsockets







Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Order No. 1991960000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376685 Oty. 50 ST Type ATPG 2.5/3 Version Order No. 2041190000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409604 Oty. 25 ST Type ATPG 2.5/5 Version Order No. 2041180000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409505 Oty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A			
GTIN (EAN) 4050118376685 Oty. 50 ST Type ATPG 2.5/3 Version Order No. 2041190000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409604 Oty. 25 ST Type ATPG 2.5/5 Version Order No. 2041180000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409505 Oty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647	Туре	ATPG 2.5 MI-R	Version
Oty. 50 ST Type ATPG 2.5/3 Version Order No. 2041190000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409604 Oty. 25 ST Type ATPG 2.5/5 Version Order No. 2041180000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409505 Oty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647	Order No.	<u>1991960000</u>	Test adapter (terminal), 1.5 mm², 250 V, 0.2 A
Type ATPG 2.5/3 Version Order No. 2041190000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409604 Order No. Otype ATPG 2.5/5 Version Order No. 2041180000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409505 Oty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A	GTIN (EAN)	4050118376685	
Order No. 2041190000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409604 Qty. 25 ST Type ATPG 2.5/5 Version Order No. 2041180000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409505 Qty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647	Qty.	50 ST	
GTIN (EAN) 4050118409604 Qty. 25 ST Type ATPG 2.5/5 Version Order No. 2041180000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409505 Qty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647	Туре	ATPG 2.5/3	Version
Qty. 25 ST Type ATPG 2.5/5 Version Order No. 2041180000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409505 Qty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647	Order No.	2041190000	Test adapter (terminal), 1.5 mm², 250 V, 0.2 A
Type ATPG 2.5/5 Version Order No. 2041180000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409505 Oty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647	GTIN (EAN)	4050118409604	
Order No. 2041180000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118409505 Qty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647	Qty.	25 ST	
GTIN (EAN) 4050118409505 Oty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647	Туре	ATPG 2.5/5	Version
Qty. 25 ST Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A GTIN (EAN) 4050118376647	Order No.	2041180000	Test adapter (terminal), 1.5 mm ² , 250 V, 0.2 A
Type ATPG 1.5-10 L Version Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A 4050118376647	GTIN (EAN)	4050118409505	
Order No. 1991890000 Test adapter (terminal), 1.5 mm², 250 V, 0.2 A 4050118376647	Qty.	25 ST	
GTIN (EAN) 4050118376647	Type	ATPG 1.5-10 L	Version
	.,,,,		
Qty. 50 ST	••	<u>1991890000</u>	
	Order No.		

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

7

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Cross-connections









The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

General	ordering data	
Туре	ZQV 2.5N/10	Version
Order No.	<u>1527690000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118447989	10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm
Qty.	20 ST	
Туре	ZQV 2.5N/10 BL	Version
Order No.	<u>1527880000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 10,
GTIN (EAN)	4050118448573	Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm
Qty.	20 ST	
Туре	ZQV 2.5N/10 RD	Version
Order No.	<u>2108910000</u>	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 10,
GTIN (EAN)	4050118486018	Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm
Qty.	20 ST	
Туре	ZQV 2.5N/2	Version
Order No.	<u>1527540000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118448467	2, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm
Qty.	60 ST	
Туре	ZQV 2.5N/2 BL	Version
Order No.	<u>1527740000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 2,
GTIN (EAN)	4050118448658	Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm
Qty.	60 ST	
Туре	ZQV 2.5N/2 RD	Version
Order No.	<u>2108470000</u>	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 2,
GTIN (EAN)	4050118448542	Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm
Qty.	60 ST	
Туре	ZQV 2.5N/20	Version
Order No.	<u>1527720000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118447972	20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm
Qty.	20 ST	
Туре	ZQV 2.5N/20 BL	Version
Order No.	<u>1527890000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 20,
GTIN (EAN)	4050118448566	Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm
Qty.	20 ST	
Туре	ZQV 2.5N/20 RD	Version
Order No.	2108920000	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 20,
GTIN (EAN)	4050118485899	Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm
Qty.	20 ST	
Туре	ZQV 2.5N/3	Version
Order No.	<u>1527570000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118448450	3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm
Qty.	60 ST	
	_	

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

_	70V 0 FN (0 P)	W :
Type	ZQV 2.5N/3 BL	Version
Order No.	<u>1527770000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 3,
GTIN (EAN)	4050118448641	Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm
Qty.	60 ST	
Туре	ZQV 2.5N/3 RD	Version
Order No.	<u>2108690000</u>	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 3,
GTIN (EAN)	4050118448535	Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm
Qty.	60 ST	
Туре	ZQV 2.5N/4	Version
Order No.	<u>1527590000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118448443	4, Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm
Qty.	60 ST	
Туре	ZQV 2.5N/4 BL	Version
Order No.	<u>1527780000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 4,
GTIN (EAN)	4050118448634	Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm
Qty.	60 ST	
Туре	ZQV 2.5N/4 RD	Version
Order No.	2108700000	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 4,
GTIN (EAN)	4050118448528	Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm
Qty.	60 ST	
Туре	ZQV 2.5N/5	Version
Order No.	1527620000	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118448436	5, Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm
Qty.	20 ST	
Туре	ZQV 2.5N/5 BL	Version
Order No.	<u>1527790000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 5,
GTIN (EAN)	4050118448627	Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm
Qty.	20 ST	1 101 III 1111 (1). 5.10, Illouided. 165, Widdi. 25.2 IIIII
Туре	ZQV 2.5N/5 RD	Version
Order No.	2108710000	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 5,
GTIN (EAN)	4050118448511	Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm
	20 ST	Filch III IIII (F). 3.10, Illsulated. 1es, Widti. 23.2 IIIII
Qty.		v ·
Туре	ZQV 2.5N/50	Version
Order No.	<u>1527730000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118411362	50, Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm
Qty.	5 ST	
Type	ZQV 2.5N/50 BL	Version
Order No.	<u>1527920000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 50,
GTIN (EAN)	4050118448559	Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm
Qty.	5 ST	
Туре	ZQV 2.5N/50 RD	Version
Order No.	2109000000	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 50,
GTIN (EAN)	4050118486001	Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm
Qty.	5 ST	
Туре	ZQV 2.5N/6	Version
Order No.	<u>1527630000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118448429	6, Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm
Qty.	20 ST	
Туре	ZQV 2.5N/6 BL	Version
Order No.	<u>1527820000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 6,
	4050118448610	Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm
GTIN (EAN)	7030110770010	
GTIN (EAN) Qty.	20 ST	

Data sheet

S2C 2.5 GY



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

_		· ·
Туре	ZQV 2.5N/6 RD	Version
Order No.	2108720000	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 6,
GTIN (EAN)	4050118448504	Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm
Qty.	20 ST	
Туре	ZQV 2.5N/7	Version
Order No.	<u>1527640000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118448412	7, Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm
Qty.	20 ST	
Туре	ZQV 2.5N/7 BL	Version
Order No.	1527830000	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 7,
GTIN (EAN)	4050118448603	Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm
Qty.	20 ST	
Туре	ZQV 2.5N/7 RD	Version
Order No.	2108810000	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 7,
GTIN (EAN)	4050118448498	Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm
Qty.	20 ST	
Туре	ZQV 2.5N/8	Version
Order No.	<u>1527670000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118448405	8, Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm
Qty.	20 ST	
Туре	ZQV 2.5N/8 BL	Version
Order No.	<u>1527840000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 8,
GTIN (EAN)	4050118448597	Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm
Qty.	20 ST	
Туре	ZQV 2.5N/8 RD	Version
Order No.	<u>2108870000</u>	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 8,
GTIN (EAN)	4050118448481	Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm
Qty.	20 ST	
Туре	ZQV 2.5N/9	Version
Order No.	<u>1527680000</u>	Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:
GTIN (EAN)	4050118447996	9, Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm
Qty.	20 ST	
Туре	ZQV 2.5N/9 BL	Version
Order No.	<u>1527870000</u>	Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 9,
GTIN (EAN)	4050118448580	Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm
Qty.	20 ST	
Туре	ZQV 2.5N/9 RD	Version
Order No.	2108900000	Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 9,
GTIN (EAN)	4050118448474	Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm
Qty.	20 ST	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	DEK 5/5 MC NE BR
Order No.	1249870000
GTIN (EAN)	4050118051865
Otv	1000 ST

Version

Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00

Weidmueller, brown

V0



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	DEK 5/5 MC NE VO WS	Version
Order No.	1388530000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4050118188622	Weidmueller, white
Qty.	1000 ST	

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	DEK 5/5 MC NE VI
Order No.	1249860000
GTIN (EAN)	4050118042764
Qty.	1000 ST

Version

Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00

Weidmueller, violet

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	DEK 5/5 MC SDR	Version
Order No.	<u>1609810000</u>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190456597	Weidmueller, To customer specification
Qty.	200 ST	

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

General	ordering data	
Туре	DEK 5/5 MC NE BL	Version
Order No.	1609801693	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397166	Weidmueller, blue
Qty.	1000 ST	
Туре	DEK 5/5 MC NE GE	Version
Order No.	1609801687	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397135	Weidmueller, yellow
Qty.	1000 ST	
Туре	DEK 5/5 MC NE GN	Version
Order No.	1609801688	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397142	Weidmueller, green
Qty.	1000 ST	
Туре	DEK 5/5 MC NE GR	Version
Order No.	<u>1609801691</u>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397159	Weidmueller, grey
Qty.	1000 ST	
Туре	DEK 5/5 MC NE OR	Version
Order No.	1238340000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4050118062632	Weidmueller, orange
Qty.	1000 ST	
Туре	DEK 5/5 MC NE RT	Version
Order No.	1609801686	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397128	Weidmueller, red
Qty.	1000 ST	
Туре	DEK 5/5 MC NE SW	Version
Order No.	1457550000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4050118263817	Weidmueller, black
Qty.	1000 ST	
Туре	DEK 5/5 MC NE WS	Version
Order No.	1609801044	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397111	Weidmueller, white
Qty.	1000 ST	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	DEK 5/5 PLUS MC NE GE	Version
Order No.	1907520000	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4032248532100	Weidmueller, yellow
Qty.	1000 ST	
Туре	DEK 5/5 PLUS MC NE WS	Version
Type Order No.	DEK 5/5 PLUS MC NE WS 1854490000	Version Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
	· ·	

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	DEK 5/5 PLUS MC SDR	Version
Order No.	<u>1854500000</u>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4032248393602	Weidmueller, To customer specification
Qty.	200 ST	

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	DEK 5/5 S MC NE WS	Version
Order No.	<u>1341620000</u>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4050118145793	Weidmueller, white
Qty.	400 ST	

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	DEK 5/5 S MC SDR	Version
Order No.	<u>1341590000</u>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4050118146042	Weidmueller, To customer specification
Qty.	80 ST	
Type	WS 10/5 M PLUS MC SDR	Version
Type Order No.	WS 10/5 M PLUS MC SDR 2007770000	Version WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.


- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	WS 10/5 M PLUS MC NE WS	Version
Order No.	2003770000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4050118424447	Allen-Bradley, white
Qty.	600 ST	
Type	WS 10/5 M MC NE WS	Version
Type Order No.	WS 10/5 M MC NE WS 1792000000	Version WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
	,	

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	WS 10/5 MC M SDR	Version
Order No.	<u>1792010000</u>	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248223879	Allen-Bradley, To customer specification
Qty.	144 ST	

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	WS 10/5 MC NE BL	Version
Order No.	<u>1773531693</u>	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248141814	Allen-Bradley, blue
Qty.	720 ST	
Туре	WS 10/5 MC NE GE	Version
Order No.	<u>1773531687</u>	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248141753	Allen-Bradley, yellow
Qty.	720 ST	
Туре	WS 10/5 MC NE RT	Version
Order No.	<u>1773531686</u>	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248141746	Allen-Bradley, red
Qty.	720 ST	
Туре	WS 10/5 MC NE WS	Version
, i		
Order No.	<u>1635000000</u>	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
	1635000000 4008190261948	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, white

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

General ordering data

Туре	WS 10/5 MC SDR	Version
Order No.	1635010000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4008190456634	Allen-Bradley, To customer specification
Qty.	144 ST	

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	WS 10/5 PLUS MC NE WS	Version
Order No.	1046380000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248782086	Allen-Bradley, white
Qty.	600 ST	

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	WS 10/5 PLUS MC SDR	Version
Order No.	1046320000	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248782024	Allen-Bradley, To customer specification
Qty.	120 ST	

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

DEK 5/5



WS/DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- · Large label field for optimal legibility
- · High flexibility thanks to manufacturer independence

General ordering data

Туре	DEK 5/5 MM WS	Version
Order No.	2007110000	Dekafix, Terminal marker, 5 x 5 mm, Weidmueller, white
GTIN (EAN)	4050118391862	
Qty.	800 ST	

WS 8/5



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- · High flexibility thanks to manufacturer independence

General ordering data

Туре	WS 8/5 MM WS	Version
Order No.	2007150000	WS, Terminal marker, 8 x 5 mm, Weidmueller, white
GTIN (EAN)	4050118392029	
Qty.	800 ST	

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.


- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	WS 8/5 MC NE BL	Version
Order No.	1773521693	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248141715	Allen-Bradley, blue
Qty.	720 ST	
Туре	WS 8/5 MC NE GE	Version
Order No.	<u>1773521687</u>	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248141548	Allen-Bradley, yellow
Qty.	720 ST	
Туре	WS 8/5 MC NE OR	Version
Order No.	<u>1773521690</u>	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248143092	Allen-Bradley, orange
Qty.	720 ST	
Туре	WS 8/5 MC NE RT	Version
Order No.	<u>1773521686</u>	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248141531	Allen-Bradley, red
Qty.	720 ST	
Туре	WS 8/5 MC NE WS	Version
Order No.	<u>1640740000</u>	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4008190279103	Allen-Bradley, white
Qty.	720 ST	

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Creation date 05.11.2025 04:35:45 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

General ordering data

Type	WS 8/5 MC SDR	Version
Order No.	<u>1640750000</u>	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4008190456627	Allen-Bradley, To customer specification
Qty.	144 ST	

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	WS 8/5 PLUS MC NE WS	Version
Order No.	<u>1951870000</u>	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248631605	Allen-Bradley, white
Qty.	600 ST	

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Creation date 05.11.2025 04:35:45 MEZ

Туре	WS 8/5 PLUS MC SDR	Version
Order No.	1038790000	WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4032248768066	Allen-Bradley, To customer specification
Qty.	120 ST	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Digital current clamp devices



Digital current clamp devices and attachments and adapters are used for measuring AC and DC currents. The significant advantage of these devices is that you can make a measurement without breaking the flow of current.

General ordering data

Type ZUB MULTIMETER
Order No. 9205270000
GTIN (EAN) 4032248723522

Qty. 1 ST

Version Multimeter

End bracket









Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type AEB 35 SC/1 BK
Order No. 2475310000
GTIN (EAN) 4050118487114
Otv. 50 ST

Version

A-series, End bracket

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

Type BZT 1 WS 10/5 Order No. <u>1805490000</u> GTIN (EAN) 4032248270231

Qty.

100 ST

Version

Accessories, Marker holder

Creation date 05.11.2025 04:35:45 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Type BZT 1 ZA WS 10/5 Order No. 1805520000

4032248270248

Qty. 100 ST

GTIN (EAN)

WS 10/5 Version

End plates and partition plates



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

Type APP 1
Order No. 2488970000
GTIN (EAN) 4050118499216
Oty. 50 ST

Version

A-series, Partition plate

Accessories, Marker holder

End bracket









Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	AEB 35 SCL/1 V0	Version
Order No.	<u>2661280000</u>	A-series, End bracket
GTIN (EAN)	4050118702163	
Qty.	20 ST	
Туре	AEB 35 SCL/1 VO BK	Version
Order No.	<u>2661300000</u>	A-series, End bracket
GTIN (EAN)	4050118702187	
Qty.	20 ST	
Туре	AEB 35 SCL/1 VO GY	Version
Type Order No.	AEB 35 SCL/1 V0 GY 2661290000	Version A-series, End bracket
Order No.	2661290000	
Order No. GTIN (EAN)	<u>2661290000</u> 4050118702170	
Order No. GTIN (EAN) Oty.	2661290000 4050118702170 20 ST	A-series, End bracket
Order No. GTIN (EAN) Oty. Type	2661290000 4050118702170 20 ST ZST 1	A-series, End bracket Version

Creation date 05.11.2025 04:35:45 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Туре ZST Version Z-series, Accessories holder

Order No. 1678680000 GTIN (EAN) 4008190466770

10 ST Qty.

End plates and partition plates



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

Туре SEP 2C 2.5 Version Order No. 2751080000 End plate for terminals, dark beige, Height: 56.9 mm, Width: 2.1 mm, GTIN (EAN) 4064675267607 V-0, Wemid, Snap-on: Yes

Qty. 20 ST

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadiummolybdenum steel, gun-metal finish.

General ordering data

1 ST

Qty.

Туре SDIS SLIM 0.6X3.5X100 Order No. 2749610000 Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade GTIN (EAN) 4050118896350 thickness (A): 0.6 mm

Creation date 05.11.2025 04:35:45 MEZ