

THM GEW FLAG 54/8 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system M-Print® PRO under Windows optimise all labelling efforts.

- High-quality polyester labels in different colours
- Due to their flexible material and the thick adhesive layer, the THM GEW can be used on angled or round objects such as cables or hoses
- Roll-packaged THM ET S7 can be used to label the Simatic 200S, S7-300 and S7-400 modules from Siemens
- Labels are automatically positioned in the printer for perfectly centred prints on each label.
- Labelling with the THM MultiMark or THM MultiMark Plus thermal transfer printers

General ordering data

Order No.	3034810000
Type	THM GEW FLAG 54/8 WS
GTIN (EAN)	4099986991699
Qty.	4000 items

THM GEW FLAG 54/8 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	54 mm	Height (inches)	2.126 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	674 g		

General data

Adhesive	Natural rubber adhesive	Material colour according to resistance code	9
Type of printing	neutral	Printing method	Thermal transfer
Width	8 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	80 °C	Operating temperature range, min.	-29 °C
Colour	white	Halogen	Yes
Basic material	Vinyl-coated cotton fabric	Printed characters	without
Size of labelling field	21.4 x 8 mm	Number per roll	4000

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	70 mm ²
Conductor cross-section, min.	0.75 mm ²	Conductor O.D., max.	12 mm
Conductor O.D., min.	1 mm	Conductor O.D.	1 - 12 mm

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		