Data sheet

THM MT30X 15/4 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Order No.	3034820000
Type	THM MT30X 15/4 GE
GTIN (EAN)	4099986991705
Qty.	10000 items

Data sheet

THM MT30X 15/4 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	0.02 g		

General data

Adhesive	Acrylate	Printing method	Thermal transfer
Version	Self-adhesive, halogen-free	Width	15 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C	Colour	yellow
Halogen	No	Basic material	Polyester
Printed characters	without	Number per roll	10000

Device markers

Halogen	No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		