

## FW R4 R1U 3.0N1 TY

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



IEEE 1394a - FireWire sockets and field-attachable plugs – flexible data connections

FireWire socket connectors from Weidmüller offer fast data transfers and easy on-site adjustment - ideal for industrial applications

Features and Benefits:

- **Robust and durable:** Designed for demanding environments with stable locking
- **EMC protection:** Reliable protection against interference for clean data transmission
- **Hot plug & play:** Devices can be connected during operation and are recognized
- **Fast and lossless transmission** up to 400 Mbit/s
- **Integrated power supply** (8 to 33 V DC, 1.5 A, max. 48 W)
- **Easy assembly** without special tools on site, with solder cup connection on the field-assembly connector

### General ordering data

Version	, PCB plug-in connector, FireWire 400, female header, 10 Gbit/s, THT/THR solder connection, 90°, Plugging cycles: , Number of poles: 6, LCP, Gold over nickel, Tray (manual assembly)
Order No.	<a href="#">3116000000</a>
Type	FW R4 R1U 3.0N1 TY
GTIN (EAN)	4099987228268
Qty.	1500 items
Packaging	Tray (manual assembly)

## FW R4 R1U 3.0N1 TY

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	18.1 mm	Depth (inches)	0.7126 inch
Height	13.5 mm	Height (inches)	0.5315 inch
Width	8.4 mm	Width (inches)	0.3307 inch
Net weight	6.67 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### System specifications

Number of poles	6	LED	No
Solder pin length (l)	1.15 mm	Mounting onto the PCB	THT/THR solder connection
Pitch in inches (P)	0.008 "	Shielding material	Copper alloy
Shielding	Yes	Side termination, characteristic	Solder flange
Transmission rate	10 Gbit/s	Number of solder pins per pole	1
Type of connection	Solder connection	Pitch in mm (P)	2.00 mm
Protection degree	IP20	Outgoing elbow	90°
Shield surface	nickel-plated	Shield tabs	none
Performance-Category	10 Gbit/s	Soldering process	Reflow soldering, Manual soldering, Wave soldering

### Electrical properties

Dielectric strength, contact / contact	100 V AC	Insulation resistance	≥ 100 MΩ
Nominal voltage	30 V		

### Material data

Insulating material	LCP	Colour	black
Colour chart (similar)	RAL 9011	Insulation resistance	≥ 100 MΩ
Moisture Level (MSL)	1	UL 94 flammability rating	V-0
Contact base material	Copper alloy	Contact material	Copper alloy
Contact surface	Gold over nickel	Storage temperature, min.	-25 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C		

### Packing

Packaging	Tray (manual assembly)	VPE length	0.00 mm
VPE width	0.00 mm	VPE height	0.00 mm

### Important note


Notes

**Technical data**

**Classifications**

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		

**Drawings**



FW R4 R1U 3.0N1 TY

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

www.weidmueller.com

