

DC SB M 50A 2POL CG 1KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Photovoltaics, Switch, Switch disconnecter, 1000 V, DC version, 50 A, Manual switch
Order No.	3123770000
Type	DC SB M 50A 2POL CG 1KV
GTIN (EAN)	4099987271981
Qty.	1 items

DC SB M 50A 2POL CG 1KV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	121.5 mm	Depth (inches)	4.7835 inch
Height	165 mm	Height (inches)	6.4961 inch
Width	140 mm	Width (inches)	5.5118 inch
Net weight	621 g		

Temperatures

Ambient temperature	-30 °C...50 °C
---------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Included in delivery

Included accessories	Article	Forked cable lugs
	Quantity	4

General data

Protection degree	IP65
-------------------	------

Classifications

ETIM 8.0	EC000216	ETIM 9.0	EC004830
ETIM 10.0	EC004830	ECLASS 14.0	27-07-02-03
ECLASS 15.0	27-07-02-03		

Tender specification sheets

Long specification	<p>Load break switch in polyester housing. Suitable for switching off the DC side. Number of poles: 2 Operating current, rated value (Ie):</p> <ul style="list-style-type: none"> - according to IEC (PV1, 1000 V): 50 A - according to IEC (PV1, 1500 V): 20 A - according to IEC (PV2, 1000 V): 20 A - according to IEC (PV2, 1500 V): 8 A <p>Rated insulation voltage (Ui):</p> <ul style="list-style-type: none"> - according to IEC: 1500 V <p>Suitability for use: Main switch: Yes Number of contacts normally open: 4</p>
--------------------	---

DC SB M 50A 2POL CG 1KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Number of contacts normally closed: 0
Number of switching positions: 2
Lockable: Yes
The switch is mounted using 4 screws.
Protection class (IP): 65
Polyester housing with M25 cable Gland with multiple sealing inserts for PV conductor with max. conductor cross-section: 6 mm².
Dimensions HxWxD: 165x140x121.5 mm.
Approval according to low voltage switchgear and controlgear IEC 60947-3, DIN VDE 0660 Part 107 (EN 60947-3)

Data sheet

DC SB M 50A 2POL CG 1KV

Drawings

