

**HDC-KIT-HA 04.406 P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The PUSH IN connection is a direct-insert method of connection. The preprocessed wire can be inserted directly into the wire connection without the need for any tools.

**General ordering data**

Version	RockStar® , HA, Installation size: 1, PUSH IN, 230 V, 10 A, Plastic, PG 11
Order No.	<a href="#">3123970000</a>
Type	HDC-KIT-HA 04.406 P
GTIN (EAN)	4099987272605
Qty.	1 items

## HDC-KIT-HA 04.406 P

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



### Dimensions and weights

Net weight 108 g

### Temperatures

Limit temperature -40 °C ... 100 °C

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC Potassium perfluorobutane sulfonate 29420-49-3

### General data

Surface finish	Powder coating	Protection degree	IP65
Series	HA		

### Version

Size of cable entries	PG 11	Number of cable entry on top	1
Number of cable entry sideways	0	Type of connection	PUSH IN
Design of locking system	Side-locking clamp on lower side	Installation size	1
Sealing	NBR	Colour (RAL)	RAL 7035
BG	1		

### General data

Number of poles	4	Connection type PE	PUSH IN connection
Installation size	1	Cable gland	PG 11
Basic material	Plastic	Series	HA
Rated voltage (DIN EN 61984)	230 V	Rated current (DIN EN 61984)	10 A
BG	1		

### Version

Type of connection	PUSH IN	Installation size	1
Conductor cross-section, max.	2.5 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Surface finish	Powder coating	Max. torque for main contact	0.55 Nm
Basic material	Plastic	Min. torque for main contact	0.5 Nm
BG	1		

### Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		