

HDC-KIT-HA 04.406 M P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The PUSH IN connection is a direct-insert method of connection. The preprocessed wire can be inserted directly into the wire connection without the need for any tools.

General ordering data

Version	RockStar® , HA, Installation size: 1, PUSH IN, 230 V, 10 A, Plastic, M 20
Order No.	3124020000
Type	HDC-KIT-HA 04.406 M P
GTIN (EAN)	4099987272698
Qty.	1 items

HDC-KIT-HA 04.406 M P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Net weight 121 g

Temperatures

Limit temperature -40 °C ... 100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC Potassium perfluorobutane sulfonate 29420-49-3

General data

Housing main material	Plastic	Surface finish	Powder-coated
Protection degree	IP65	Series	HA
EMC housings	No		

Version

Size of cable entries	M 20	Number of cable entry on top	1
Number of cable entry sideways	0	Type of connection	PUSH IN
Design of locking system	Side-locking clamp on lower side	Installation size	1
Sealing	NBR	Colour (RAL)	RAL 7035
BG	1		

General data

Number of poles	4	Connection type PE	PUSH IN connection
Installation size	1	Cable gland	M 20
Basic material	Plastic	Series	HA
Rated voltage (DIN EN 61984)	230 V	Rated current (DIN EN 61984)	10 A
BG	1		

Version

Type of connection	PUSH IN	Installation size	1
Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Surface finish	Powder-coated	Max. torque for main contact	0.55 Nm
Basic material	Plastic	Min. torque for main contact	0.5 Nm
BG	1		

Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		