

U-VIEW-PWEB-ES-RT-2000/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

This product is only available in combination with a u-view Advanced Touch Panel



HMI runtimes for u-view Advanced Touch Panels

By combining u-view Advanced Touch Panels with the web-based HMI software PROCON-WEB Embedded Systems, the perfect visualization solution is created – powerful software meets high-quality hardware.

To implement the optimal web-based HMI solution, PROCON-WEB Embedded Systems offers the following features:

- Role- and rights-based user management
- Comprehensive alarming
- Predefined controls such as buttons, sliders, text fields, or image areas
- Powerful complex controls such as iframes, charts, tables
- Flexible scripting for maximum adaptability
- Historian functionality for storing and visualizing historical data
- Connection to the u-OS controller via communication driver

General ordering data

Version	Visualization software, Platform for runtime system: Windows, Linux, Docker, Number of process variables, max.: 2000, Number of HMI-devices, max.: 2
Order No.	3151090000
Type	U-VIEW-PWEB-ES-RT-2000/2
Qty.	1 items

U-VIEW-PWEB-ES-RT-2000/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0 g

Environmental Product Compliance

RoHS Compliance Status Not affected
 REACH SVHC No SVHC above 0.1 wt%

Features of the runtime

Number of HMI-devices, max. 2

Licence information

Number of process variables, max. 2000

System requirements

Operating system Windows, Linux, u-OS Minimal disk space needed 0.1 GB
 Minimal memory (RAM) needed 0.1 GB

Classifications

ETIM 6.0	EC001416	ETIM 7.0	EC001416
ETIM 8.0	EC001416	ETIM 9.0	EC001416
ETIM 10.0	EC001416	ECLASS 9.0	27-24-25-02
ECLASS 9.1	27-24-25-02	ECLASS 10.0	27-24-25-02
ECLASS 11.0	27-24-25-02	ECLASS 12.0	27-24-25-02
ECLASS 13.0	27-24-25-02	ECLASS 14.0	27-24-25-02
ECLASS 15.0	27-24-25-02		