

**CMA-A30-300-333MV-1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Plug-on current transformers**

Plug-on current transformers are used wherever high currents of up to 5000A need to be measured and processed. Our plug-on current transformers supply secondary currents of 1A or 5A. Weidmüller also offers compact low-power current transformers to convert currents of up to 600 A to voltages of up to 333 mV.

**General ordering data**

Version	Primary current: 300 A, Secondary current max.: 1 A, Load: 20 VA, Tolerance class: 1
Order No.	<a href="#">3154180000</a>
Type	CMA-A30-300-333MV-1
GTIN (EAN)	4099987646048
Qty.	1 items

## CMA-A30-300-333MV-1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	57.4 mm	Depth (inches)	2.2598 inch
Height	78.2 mm	Height (inches)	3.0787 inch
Width	65.4 mm	Width (inches)	2.5748 inch
Diameter	30 mm	Net weight	207 g

### Temperatures

Storage temperature	Operating temperature	-5 °C...40 °C
---------------------	-----------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Measuring voltage input

Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
-----------------------	-------	-----------------------	-------

### Electrical attributes

Tolerance class	1	Secondary current	1 A
Load	20 VA	Primary current	300 A

### Technical properties

Protection degree	IP20	Measurement accuracy	1%
Thermal rated continuous current I <sub>thermal</sub>	1.2 x I <sub>rated</sub>	Nominal frequency	50 / 60 Hz

### Input

Input frequency	50/ 60 Hz
-----------------	-----------

### Insulation coordination

Tolerance class	1	Insulation voltage	3 kV / 1 min
-----------------	---	--------------------	--------------

### Classifications

ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		