Data sheet

MPS 6/04 S M2 TN B B

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image





General ordering data

Version	, female plug, Pitch in mm (P): 6.35 mm, Number of poles: 4, 180°, Box
Order No.	3160630000
Type	MPS 6/04 S M2 TN B B
GTIN (EAN)	4099987676885
Qty.	48 items
Product data	IEC: 600 V / 47.2 A / 0.75 - 6 mm² UL: 300 V / 26.5 A
Packaging	Box

Data sheet

MPS 6/04 S M2 TN B B

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	49.02 mm	Depth (inches)	1.9299 inch
Height	25.32 mm	Height (inches)	0.9968 inch
Width	34.55 mm	Width (inches)	1.3602 inch
Net weight	0 g		

System Parameters

Product family	OMNIMATE 4.0	Type of connection	Board connection
Pitch in mm (P)	6.35 mm	Pitch in inches (P)	0.250 mm
Number of poles	4	L1 in mm	19.05 mm
L1 in inches	0.750 "	Number of rows	1
Pin series quantity	1	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch
Touch-safe protection acc. to DIN VDE 0470	IP 20	Protection degree	IP20
Volume resistance	≤5 mΩ	Plugging cycles	≥ 25
Plugging force per pole, max.	12 N	Pulling force per pole, max.	10 N

Material data

Insulating material	PA 9T	Colour	black
Colour of operational elements	orange	Colour chart (similar)	RAL 9011
Comparative Tracking Index (CTI)	≤ 600	Moisture Level (MSL)	1
UL 94 flammability rating	V-0	Contact base material	CuMg
Contact material	Cu-alloy	Contact surface	tinned
Tinning type	matt	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	125 °C		

Conductors suitable for connection

Conductor cross-section (rated connection), min.	0.5 mm²	Conductor cross-section (rated connection), max.	6 mm²
Solid, min. H05(07) V-U	0.75 mm²	Solid, max. H05(07) V-U	4 mm²
Flexible, min. H05(07) V-K	0.75 mm²	Flexible, max. H05(07) V-K	6 mm²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.5 mm²	w. plastic collar ferrule, DIN 46228 pt 4, max.	4 mm²
w. wire end ferrule, DIN 46228 pt 1, min.	0.75 mm²	w. wire end ferrule, DIN 46228 pt 1, max.	4 mm²

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current at min. number of poles (Tu = 20 °C)	47.2 A
Rated current, max. number of poles (Tu=20°C)	41 A	Rated current, min. number of poles (Tu=40°C)	42.5 A
Rated current at max. number of poles (Tu = 40 °C)	36.8 A	Rated voltage for surge voltage class (pollution degree II/2)	600 V
Rated voltage for surge voltage class (pollution degree III/2)	800 V	Rated voltage for surge voltage class (pollution degree III/3)	630 V
Rated impulse voltage for surge voltage class (pollution degree III/2)	6 kV	Rated impulse voltage for surge voltage class (contamination degree III/3)	6 kV
Creepage distance, min.	11.2 mm	Clearance, min.	11.2 mm

MPS 6/04 S M2 TN B B

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Rated data acc. to UL 1059

Rated voltage (Use group B / UL 1059)	300 V	Rated voltage (Use group D / UL 1059)	600 V
Rated voltage (Use group F / UL 1059)	1000 V	Rated current (Use group B / UL 1059)	26.5 A
Rated current (Use group C / UL 1059)	26.5 A	Rated current (Use group D / UL 1059)	5 A

Important note

Notes	• Rated current related to rated cross-section & min. No. of poles. • P on drawing = pitch • Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards. • Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Classifications

ETIM 8.0	EC002638	ETIM 9.0	EC002638
ETIM 10.0	EC002638	ECLASS 14.0	27-46-02-02
ECLASS 15.0	27-46-02-02		

MPS 6/04 S M2 TN B B

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Product image

