

**US67-VIB24C-IOL-0UNI0002A00000**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Weidmüller provides high-quality wired vibration sensors for monitoring vibrations in various frequency and measuring ranges.

**General ordering data**

Order No.	3094640000
Type	<a href="#">US67-VIB24C-IOL-0UNI0002A00000</a>
GTIN (EAN)	4099987114455
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-07-30T00:00:00+02:00

US67-VIB24C-IOL-0UNI0002A00000

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E337701

Dimensions and weights

Depth	27.7 mm	Depth (inches)	1.0905 inch
Height	72.5 mm	Height (inches)	2.8543 inch
Width	23.8 mm	Width (inches)	0.937 inch
Diameter	27.7 mm	Net weight	90 g

Temperatures

Storage temperature	-40 °C...80 °C	Ambient temperature	-40 °C...80 °C
Operating temperature	-40 °C...80 °C	Humidity	0...100%

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	438dfa95-6948-44c9-aa1b-107ba9482546

General data

Safety category	No	Applications	for indoor and outdoor use
Operating life	10 years	For Ex zone dust	None
For Ex zone gas	None	Machine vibration assessment included	Yes
Protection class (UL)	Type 4X	Protection degree	IP67 (in plugged condition), IP66 (in plugged condition)

Sensor

Physical measurement principle of the sensor	Vibration acceleration		
Frequency range configurable	Yes		
Vibration acceleration, min. (gravity g)	-48		
Sensor temperature	Monitored value	Temperature	
	Type of sensor	Temperature MEMS	
	Measurement accuracy	+/-1°C	
Cross sensitivity	<5 %		
Temperature range measuring head	Temperature, min.	-40 °C	
	Temperature, max.	85 °C	
Effective vibration velocity, max.	64 mm/s		
Device is calibrated	Yes		
Sensor measuring method acc. to ISO 10816-3	1-axis broadband analysis 10 Hz...1 kHz, VRMS		
Accuracy of vibration measurement	10 %		
Calibration point	1g (rms) @ 159,2 Hz		
Vibration acceleration, max. (gravity g)	48		

## US67-VIB24C-IOL-0UNI0002A00000

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

Measurement range	Configurable via IO-Link		
Measuring unit vibration velocity (RMS)	mm/s		
Accuracy of temperature measurement	1 %		
Number of measuring axes	1		
Temperature measurement available	Yes		
Transmission interval of signals	Continuous measurement		
Spectral analysis method (FFT)	No FFT calculation		
Frequency range, min.	1 Hz		
Frequency range, max.	12000 Hz		
Sensor vibration	Monitored value	Acceleration	
	Type of sensor	single-axis MEMS	
Monitoring	Vibration monitoring acc. to DIN ISO 10816-3		
Accuracy	±10 % (acc. DIN ISO 2954), ±0,5 % at the calibration point		

### Cable

Number of poles	4	Plug	1x M12 female 4-pole
Connection type	M12		

### Electrical data

Output level	N/O contact / N/C contact (low-active / high-active)	Output signal	4...20 mA (proportional to measuring range)
Input current, max.	320 mA	No-load input current	120 mA
IO-Link available	Yes	Measuring and process variables	RMS vibration acceleration, RMS vibration velocity, Peak value vibration acceleration, Temperature, Status of the internal self-test, Error status, States of all switching signals, Crest value, Bearing condition parameter according to 13337-3
Connection type of IO-Link interface	IO-Link V1.1.3		

### Housing

Basic material	Stainless steel 1.4305 (V2A), AISI 303 (standard)		
----------------	---	--	--

### Installation

Connection thread	M8 thread	Tightening torque	8 Nm
Type of mounting	Screw mounting, Direct mounting, Adhesive fastening, Mounting plate, Magnet, Miscellaneous	Type of thread	External thread
Type of mounting sensor	Many possibilities using adapters, Direct mounting: screw connection	Wrench size	24 mm
Torque for cap nut, max.	0.40 Nm	Mounting thread	M8
Installation location	Indoor and outdoor use	Sealing with tie possible	No

### Power supply

Type of power supply	DC, External	Wireless	No
----------------------	--------------	----------	----

**US67-VIB24C-IOL-OUNI0002A00000****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Measuring voltage input**

Frequency range, max.	12000 Hz	Frequency range, min.	1 Hz
-----------------------	----------	-----------------------	------

**Classifications**


ETIM 8.0	EC004309	ETIM 9.0	EC004309
ETIM 10.0	EC004309	ECLASS 14.0	27-20-14-12
ECLASS 15.0	27-20-14-12		

**US67-VIB24C-IOL-0UNI0002A00000**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

[www.weidmueller.com](http://www.weidmueller.com)



## US67-VIB24C-IOL-0UNI0002A00000

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Sensor accessories

Weidmüller offers high-quality cables, plugs, mounting adapters and magnets for the professional and industrial installation of vibration monitors.



### General ordering data

Type	US67-CAB-00C4S-00150-000	Version
Order No.	<a href="#">3074570000</a>	
GTIN (EAN)	4099987075923	
Qty.	1 ST	
Type	US67-CAB-00C4S-00500-000	Version
Order No.	<a href="#">3074580000</a>	
GTIN (EAN)	4099987075930	
Qty.	1 ST	
Type	US67-CAB-00C4S-01000-000	Version
Order No.	<a href="#">3074590000</a>	
GTIN (EAN)	4099987075947	
Qty.	1 ST	
Type	US67-MNT-00M08-000M8 -C...	Version
Order No.	<a href="#">3069470000</a>	
GTIN (EAN)	4099987067591	
Qty.	1 ST	
Type	US67-MNT-00M08-003/8-000	Version
Order No.	<a href="#">3073540000</a>	
GTIN (EAN)	4099987075787	
Qty.	1 ST	
Type	US67-MNT-00M08-00M06-000	Version
Order No.	<a href="#">3069360000</a>	
GTIN (EAN)	4099987067539	
Qty.	1 ST	
Type	US67-MNT-00M08-00M10-S24	Version
Order No.	<a href="#">3073200000</a>	
GTIN (EAN)	4099987075718	
Qty.	1 ST	
Type	US67-MNT-00M08-00M12-S24	Version
Order No.	<a href="#">3073300000</a>	
GTIN (EAN)	4099987075732	
Qty.	1 ST	
Type	US67-MNT-00M08-00M16-000	Version
Order No.	<a href="#">3073330000</a>	
GTIN (EAN)	4099987075749	
Qty.	1 ST	

**US67-VIB24C-IOL-0UNI0002A00000**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

Type	US67- MNT-00M08-00M20-000	Version
Order No.	<a href="#">3073360000</a>	
GTIN (EAN)	4099987075756	
Qty.	1 ST	
Type	US67- MNT-00M08-00M24-000	Version
Order No.	<a href="#">3073370000</a>	
GTIN (EAN)	4099987075763	
Qty.	1 ST	
Type	US67- MNT-00M08-00M30-000	Version
Order No.	<a href="#">3073380000</a>	
GTIN (EAN)	4099987075770	
Qty.	1 ST	
Type	US67-MNT-00M08-01/2B-000	Version
Order No.	<a href="#">3073690000</a>	
GTIN (EAN)	4099987075817	
Qty.	1 ST	
Type	US67-MNT-00M08-01/4N-000	Version
Order No.	<a href="#">3073570000</a>	
GTIN (EAN)	4099987075800	
Qty.	1 ST	
Type	US67-MNT-00M08-01/4U-000	Version
Order No.	<a href="#">3073550000</a>	
GTIN (EAN)	4099987075794	
Qty.	1 ST	
Type	US67-MNT-00M08-OGLUE-000	Version
Order No.	<a href="#">3073700000</a>	
GTIN (EAN)	4099987075824	
Qty.	1 ST	
Type	US67- MNT-00M08-OMAG1-000	Version
Order No.	<a href="#">3073740000</a>	
GTIN (EAN)	4099987075831	
Qty.	1 ST	
Type	US67- MNT-00M08-OMAG2-000	Version
Order No.	<a href="#">3073750000</a>	
GTIN (EAN)	4099987075855	
Qty.	1 ST	