

IE-INJ-EL01-1GTPOE++

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Features of EcoLine Power-over-Ethernet unmanaged switches/injectors

- Variants with 2, 4 or 8 IEEE 802.3af/at compliant PoE ports (up to 30 watt power output per PoE port)
- Integrated DC/DC converter for providing PoE voltage to PDs over the entire PSE input voltage range from 12 to 57 V DC
- Models supporting Gigabit Ethernet including Jumbo Frame support for applications with high demand on bandwidth and latency
- Models with fiber optic ports for communication links over long distances
- Suitable for use in harsh industrial environment thanks to rugged design and wide operating temperature range of -40°C up to 75°C
- Reliable operation due to redundant voltage inputs, fault relay and LED diagnostics

General ordering data

Version	PoE Injector, Gigabit Ethernet, Number of ports: 1x RJ45 10/100/1000BaseT(X), 1x RJ45 10/100/1000BaseT(X) PoE++, IP30, -40 °C...75 °C
Order No.	3174750000
Type	IE-INJ-EL01-1GTPOE++
GTIN (EAN)	4099987855921
Qty.	1 items

IE-INJ-EL01-1GTPOE++

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E141197

Dimensions and weights

Depth	70 mm	Depth (inches)	2.7559 inch
Height	95 mm	Height (inches)	3.7401 inch
Width	41 mm	Width (inches)	1.6142 inch
Net weight	329 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

Free fall	According to IEC 60068-2-31	EMC standards	EN 55032, EN 55035, FCC Part 15 Subpart B Class A, IEC 61000-4-2 Class A, IEC 61000-4-3 RS: 80 MHz - 5 GHz: 3 V/m, IEC 61000-4-4 EFT: Power: 0.5 kV; Signal: 0.5 kV, IEC 61000-4-5 Surge: Power: 0.5 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 Vrms
Vibration	according to IEC 60068-2-6	Shock	according to IEC 60068-2-27
Safety standard	UL 61010-1, UL 61010-2-201		

Environmental conditions

Operating temperature, max.	75 °C		
Operating temperature, min.	-40 °C		
Humidity	5 to 95 % (non-condensing)		
Storage temperature, max.	85 °C		
Storage temperature, min.	-40 °C		
Operating altitude	Altitude, max.	2000 m	
	Note	in acc. with UL	
	Altitude, max.	6000 m	
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads	

Guarantee

Time interval 5 years

IE-INJ-EL01-1GTPOE++

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Interfaces

RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port	Number of ports	1x RJ45 10/100/1000BaseT(X), 1x RJ45 10/100/1000BaseT(X) PoE++
LED indicator	Power LED: PWR, PoE active		

MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	1834973 h
	Ambient temperature	25 °C

Power over Ethernet (PoE)

PoE output power	Standard	IEEE 802.3af
	Output power	15.4 W
	Standard	IEEE 802.3at
	Output power	30 W
	Standard	IEEE 802.3bt
	Output power	90 W
Total PoE power budget	Voltage type	DC
	Voltage, min.	12 V
	Voltage, max.	23.9 V
	Power budget	30 W
	Voltage type	DC
	Voltage, min.	24 V
	Voltage, max.	57 V
	Power budget	90 W
PoE pin assignment	Mode A: Pin 1, 2 (V-); Pin 3, 6 (V+); Alternative A; MDI-X / Mode B: Pin 4, 5 (V+); Pin 7, 8 (V-); Alternative B; MDI-X	

Power supply

Reverse polarity protection	Yes	
Supply voltage	12/24/48 V DC, 1 single input	
Overload current protection	Yes	
Connection type	1 removable 4-pin terminal block	
Voltage supply range	Voltage type	DC
	Voltage, min.	12 V
	Voltage, max.	57 V
Current consumption	Voltage	12 V
	Voltage type	DC
	Current consumption with Powered Device (PD)	2.54 A
	Current consumption without Powered Device (PD)	0.11 A
	Voltage	24 V
	Voltage type	DC
	Current consumption with Powered Device (PD)	3.82 A
	Current consumption without Powered Device (PD)	0.07 A
	Voltage	48 V
	Voltage type	DC
	Current consumption with Powered Device (PD)	1.9 A
	Current consumption without Powered Device (PD)	0.01 A

IE-INJ-EL01-1GTPOE++

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Technical data

Housing main material	Metal	Type of mounting	DIN rail
Protection degree	IP30	Speed	Gigabit Ethernet

Technology

Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3ab for 1000BASE-T, IEEE 802.3at/af/bt for Power-over-Ethernet
----------	--

Classifications

ETIM 8.0	EC003552	ETIM 9.0	EC003552
ETIM 10.0	EC003552	ECLASS 14.0	19-17-04-10
ECLASS 15.0	19-17-04-10		

IE-INJ-EL01-1GTPOE++

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version	
Order No.	1241440000	Kit for 19"-rack mounting	
GTIN (EAN)	4050118029154		
Qty.	1 ST		