

WIL-VRGBW-FPPF-XXXX-X265-F**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The WIL-Vario is a robust LED light for industrial applications that offers maximum individuality. It has a fully encapsulated aluminum housing, is IP67-rated, and is suitable for demanding environments. Thanks to the WS2812B protocol, each LED diode can be individually controlled in terms of color, brightness, and function.

The light operates at a rated voltage of 5 V DC. Its gap-free stackability makes it ideal for applications such as level indicators, area markings, or spot lighting.

General ordering data

Order No.	3201450000
Type	WIL-VRGBW-FPPF-XXXX-X265-F
GTIN (EAN)	4099987989190
Qty.	1 items

WIL-VRGBW-FPPF-XXXX-X265-F

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	10 mm	Depth (inches)	0.3937 inch
Height	10 mm	Height (inches)	0.3937 inch
Length	265 mm	Length (inches)	10.433 inch
Net weight	205 g		

Temperatures

Operating temperature	-20 - 50°C
-----------------------	------------

Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Housing main material	Aluminium	Cable length	5 m

Connection data

Connection thread	without
-------------------	---------

Electric data

Power	1.2 W	Dimmable	Yes
-------	-------	----------	-----

General technical data

Shape of the LED module	Rectangular	Operating life	60.000 h
Protection degree	IP67	Efficiency class (according to EU Directive No. 874/2012)	Not required

Material data

Housing main material	Aluminium	Encapsulation compound	PUR V0
-----------------------	-----------	------------------------	--------

Classifications

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		

