


SPE P20 R1H 2.1 6 YG/YG RL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**SPElink®****Single Pair Ethernet PCB sockets**

Single pair Ethernet is a technology that only requires one pair of wires to transmit data and power.

The resulting benefits will make SPE the preferred network at the field level and beyond.

Advantages of Single Pair Ethernet:

- Consistent: Single Pair Ethernet enables uniform Ethernet-based communication from the sensor to the cloud
- Future-proof: key technology for Industry 4.0 and IIoT
- Flexible: ranges of up to 1000 m and transmission properties of up to 1 Gbps enable use across applications
- Innovative: lighter, less space required, and reduced installation effort

General ordering data

Version	PCB plug-in connector, SPE (Single Pair Ethernet), Clip-on flange, THT/THR solder connection, 1.80 mm, Number of poles: 2, 90°, Solder pin length (l): 2.1 mm, Ni/Au, black, Tube
Order No.	3234510000
Type	SPE P20 R1H 2.1 6 YG/YG RL
GTIN (EAN)	4069166023052
Qty.	100 items
Packaging	Tube

SPE P20 R1H 2.1 6 YG/YG RL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	21.5 mm	Depth (inches)	0.8465 inch
Height	10.3 mm	Height (inches)	0.4055 inch
Height of lowest version	10.3 mm	Width	9 mm
Width (inches)	0.3543 inch	Net weight	1.64 g

Temperatures

Installation temperature	-40 °C ... 85 °C
--------------------------	------------------

System specifications

Number of poles	2	LED	Yes
Solder pin length (l)	2.1 mm	Mounting onto the PCB	THT/THR solder connection
Pitch in inches (P)	0.071 "	Shielding material	CuSn
Shielding	Yes	Side termination, characteristic	Clip-on flange
Transmission rate	10/100/1000 MBit/s	Number of solder pins per pole	1
Type of connection	Solder connection	Category	CAT B (ISO/IEC 63171)
Product family	OMNIMATE Data - Single Pair Ethernet	Pitch in mm (P)	1.80 mm
Protection degree	IP20	Plugging cycles	750
Model	Socket connector	Outgoing elbow	90°
Shield surface	tinned	Colour of right LED	Green/yellow
Shield tabs	none	Performance-Category	CAT B (ISO/IEC 63171) 10/100/1000 MBit/s
Soldering process	Reflow soldering, Manual soldering, Wave soldering	Latch option	top
Solder pin dimensions	Octagonal	Colour of left LED	Green/yellow

Electrical properties

Dielectric strength, contact / shield	2250 V DC	Dielectric strength, contact / contact	1000 V DC
Insulation resistance	≥ 500 MΩ	Nominal voltage	72 V
PoE / PoE+	PoDL acc. to IEEE 802.3bu / cg		

Material data

Insulating material	PA 9T	Colour	black
Colour chart (similar)	RAL 9011	Insulation resistance	≥ 500 MΩ
Moisture Level (MSL)	1	UL 94 flammability rating	V-0
Contact base material	CuMg	Contact material	Cu-alloy
Contact surface	Ni/Au	Layer structure of solder connection	2...4 µm Ni / ≥ 0.25 µm Au
Storage temperature, min.	-40 °C	Storage temperature, max.	85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C

Packing

Packaging	Tube	VPE length	5.00 mm
VPE width	4.00 mm	VPE height	3.00 mm

Important note

Notes

SPE P20 R1H 2.1 6 YG/YG RL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		