

QL 2 ST5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

| | |
|------------|--|
| Version | Cross-connector (terminal), when screwed in, grey, 41 A, Number of poles: 2, Pitch in mm (P): 16.30, Insulated: No, Width: 17.5 mm |
| Order No. | 3834300000 |
| Type | QL 2 ST5 |
| GTIN (EAN) | 4008190456955 |
| Qty. | 20 items |

QL 2 ST5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 1 mm | Depth (inches) | 0.0394 inch |
| Height | 16.3 mm | Height (inches) | 0.6417 inch |
| Width | 17.5 mm | Width (inches) | 0.689 inch |
| Net weight | 2.35 g | | |

Temperatures

| | | | |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|-------|--------|------|
| Basic material | Cu Zn | Colour | grey |
|----------------|-------|--------|------|

System specifications

| | |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

Additional technical data

| | | | |
|----------------|-----------------|--------------------------|----|
| Type of fixing | when screwed in | Explosion-tested version | No |
|----------------|-----------------|--------------------------|----|

Dimensions

| | |
|-----------------|----------|
| Pitch in mm (P) | 16.30 mm |
|-----------------|----------|

General

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Rating data

| | | | |
|--------------------------|-------|-----------------|------|
| Rated voltage | 400 V | Nominal current | 41 A |
| Current at maximum wires | 41 A | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |