


**FUSEHOLDER WSFH 10X85 1K5V**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Photovoltaic fuse holder for PV applications

- For usage in photovoltaic DC combiner boxes up to 1500V
- DIN- rail mounted
- For use with cylindrical fuse links from 15A up to 32A of 10x85mm gPV

**General ordering data**

Version	Photovoltaics, Fuse holder, 1500 V, 10x85
Order No.	<a href="#">4000002613</a>
Type	FUSEHOLDER WSFH 10X85 1K5V
GTIN (EAN)	8430243419512
Qty.	10 items

## FUSEHOLDER WSFH 10X85 1K5V

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	67 mm	Depth (inches)	2.6378 inch
Height	125 mm	Height (inches)	4.9212 inch
Width	22.2 mm	Width (inches)	0.874 inch
Net weight	10 g		

### Temperatures

Operating temperature	-50°C to +90°C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	90 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Fuse holder connection

Number of connections	2	Stripping length	9.5 mm
Tightening torque, max.	2.5 Nm	Tightening torque, min.	2 Nm
Type of connection	Screw connection	Wire material	Copper
Wire connection cross section AWG, min.	AWG 6	Wire connection cross section AWG, max.	AWG 17
Wire connection cross section, finely stranded, min.	1 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	16 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	1 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	16 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	1 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	16 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	1 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	16 mm <sup>2</sup>

### Fuse holder technical data

Cartridge fuse	10 x 85 mm	Colour	Light Blue
Display	Without LED	Fuse holder (cartridge holder)	Pivoting
Max. current	32 A	Number of potentials	1
Power dissipation, max.	6.5 W	Mounting rail	TS 35
Rated impulse withstand voltage	6 kV	Surge voltage category	III
Type of mounting	TS 35		

### Classifications

ETIM 8.0	EC000899	ETIM 9.0	EC000899
ETIM 10.0	EC000899	ECLASS 14.0	27-25-01-13
ECLASS 15.0	27-25-01-13		