


PTSC KB40X14**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The RS 100 Profi offers you a flexible solution for your mounting needs, as both DIN rail mounting and wall mounting are possible. This versatility facilitates integration into different environments and applications. The housing can be used for the Eurocard PCB standard. The profile can be cut to size so that you can adapt it precisely to your specific requirements. For particularly heavy components, additional locking feet can be used to improve stability and thus increase the safety of your installation.

Another practical feature is the option of using a cover profile to protect large components.

General ordering data

| | |
|------------|--|
| Version | Mounting screw (Terminal), 0.00 mm, Steel, Depth: 7 mm, Width: 16.9 mm, Height: 7 mm |
| Order No. | 4019420000 |
| Type | PTSC KB40X14 |
| GTIN (EAN) | 4008 190243029 |
| Qty. | 100 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 7 mm | Depth (inches) | 0.2756 inch |
| Height | 7 mm | Height (inches) | 0.2756 inch |
| Width | 16.9 mm | Width (inches) | 0.6654 inch |
| Net weight | 1.13 g | | |

Temperatures

| | |
|---------------------|---------------|
| Ambient temperature | -5 °C...40 °C |
|---------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|---------------|----------------|-------|
| Surface finish | Miscellaneous | Basic material | Steel |
|----------------|---------------|----------------|-------|

General data

| | | | |
|--------|------|------------------------|----------|
| Colour | grey | Colour chart (similar) | RAL 7035 |
|--------|------|------------------------|----------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ETIM 10.0 | EC002848 | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 | | |