

EPAK-PCI-VO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The analogue converters of the EPAK series are characterised by their compact design.

The wide range of functions available with this series of analogue converters make them suitable for applications which do not require international approvals.

Properties:

- Safe isolation, conversion and monitoring of your analogue signals
- Configuration of the input and output parameters directly on the device via DIP switches
- No international approvals
- High interference resistance

General ordering data

Version	Signal converter / insulator, Input : 4-20 mA, Output : 0-10 V, Supply voltage: 20...30 V DC
Order No.	7760054177
Type	EPAK-PCI-VO
GTIN (EAN)	6944 169701481
Qty.	1 items

EPAK-PCI-VO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	89 mm	Depth (inches)	3.5039 inch
Height	100 mm	Height (inches)	3.937 inch
Width	17.5 mm	Width (inches)	0.689 inch
Length	100 mm	Length (inches)	3.937 inch
Net weight	80 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
---------------------	----------------	-----------------------	----------------

Probability of failure

SIL in compliance with IEC 61508 None

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	7a, 7cl		
REACH SVHC	Lead 7439-92-1		
SCIP	6a722fc5-2d22-41b4-9544-5b95e45a4b77		

Input

Sensor supply	≥ 18 V @ 20 mA	Input current	4...20 mA
Input resistance, current	≤ 100 Ω		

Output

Number of outputs	1	load impedance voltage	≥ 10 kΩ
Output voltage, note	0...10 V		

Output (digital)

Rated switching current	0.1 A	Number of digital outputs	0
Max. switching voltage, AC	0 V	Max. switching voltage, DC	0 V

Output (analogue)

Number analogue outputs 1

General data

Accuracy	0.15 % v. FSR	Protection degree	IP20
Supply voltage	20...30 V DC	Step response time	≤ 100 ms
Power consumption	<60mA @ 24VDC	Temperature coefficient	≤ 150 ppm/K
Nominal power consumption	1.7 VA	Configuration	none

EPAK-PCI-VO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Insulation coordination

Impulse withstand voltage	3 kV (1.2/50µs)	EMC standards	EN 61326
Surge voltage category	III	Pollution severity	2
Galvanic isolation	between input / output / supply	Insulation voltage	2 kVeff
Rated voltage	300 V ACrms		

Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2 mm ²
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

Classifications

ETIM 8.0	EC002653	ETIM 9.0	EC002653
ETIM 10.0	EC002653	ECLASS 14.0	27-21-01-20
ECLASS 15.0	27-21-01-20		

EPAK-PCI-VO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

