

**HDC HDD 48 MC EX 1500**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The option of separating cables in Zone 2 that comply with the following approvals ATEX: T II 3G Ex ec IIC T6 Gc or IECEX: Ex ec IIC T6 Gc simplifies installation, service and enables better preparation. The approved connectors offered here must always be used complete with the corresponding approved housings and inserts and may only be disconnected without load.

**General ordering data**

Version	HDC insert, Male, 1500 V, Number of poles: 48, Crimp connection, Installation size: 8
Order No.	<a href="#">3116670000</a>
Type	HDC HDD 48 MC EX 1500
GTIN (EAN)	4099987235792
Qty.	1 items

## HDC HDD 48 MC EX 1500

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

## Approvals



UL File Number Search

[UL Website](#)

Certificate No. (cURus)

E92202

## Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Width	84 mm	Width (inches)	3.3071 inch
Net weight	80.2 g		

## Temperatures

Limit temperature -20 °C ... 40 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Chemical resistance	Substance	Acetone
	Chemical resistance	Resistant
	Substance	Ammonia, watery
	Chemical resistance	Conditionally resistant
	Substance	Petrol
	Chemical resistance	Resistant
	Substance	Benzene
	Chemical resistance	Resistant
	Substance	Diesel oil
	Chemical resistance	Conditionally resistant
	Substance	Acetic acid, concentrated
	Chemical resistance	Resistant
	Substance	Potassium hydroxide
	Chemical resistance	Conditionally resistant
	Substance	Methanol
	Chemical resistance	Conditionally resistant
	Substance	Motor oil
	Chemical resistance	Conditionally resistant
	Substance	Lye, diluted
	Chemical resistance	Resistant
	Substance	Hydrochlorofluorocarbons
	Chemical resistance	Conditionally resistant
	Substance	Outdoor use
	Chemical resistance	Conditionally resistant

## Dimensions

Width	84 mm
-------	-------

## General data

Number of poles	48	Type of connection	Crimp connection
Installation size	8	UL 94 flammability rating	V-0

## HDC HDD 48 MC EX 1500

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Colour	grey	Insulating material	Polycarbonate
Type	Male	Series	HDD
Rated voltage (DIN EN 61984)	1500 V	Free from halogens	false
BG	8	Protection degree	IP55

## Rating data IECEx/ATEX

Certificate No. (IECEx)	TUEV24ATEX9197X	Current (IECEx)	3 A
Current (ATEX)	3 A	Certificate No. (ATEX)	IECExTUR24.0077X
Wire cross section max. (IECEx)	2.5 mm <sup>2</sup>	Max. voltage (ATEX)	250 V
Wire cross section max. (ATEX)	2.5 mm <sup>2</sup>	Max. voltage (IECEx)	250 V

## Version

Stripping length, rated connection	8 mm	Type of connection	Crimp connection
Installation size	8	Conductor cross-section, max.	2.5 mm <sup>2</sup>
Conductor cross-section, min.	0.5 mm <sup>2</sup>	BG	8


## Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		

**HDC HDD 48 MC EX 1500**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

## HDC HDD 48 MC EX 1500

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## DSTV



Various accessories are available for our inserts. This includes coding elements for the inserts.

## General ordering data

Type	DSTV COBU5	Version
Order No.	<a href="#">1471500000</a>	Heavy-duty connectors, Accessories, Coding element
GTIN (EAN)	4008190178543	
Qty.	100 ST	
Type	DSTV COST4	Version
Order No.	<a href="#">1471300000</a>	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190017354	
Qty.	100 ST	

## Size 8 (24B)



The option of separating cables in Zone 2 that comply with the following approvals ATEX: T II 3G Ex ec IIC T6 Gc or IECEx: Ex ec IIC T6 Gc simplifies installation, service and enables better preparation. The approved connectors offered here must always be used complete with the corresponding approved housings and inserts and may only be disconnected without load.

## General ordering data

Type	HDC 24B AS ATEX	Version
Order No.	<a href="#">3139930000</a>	HDC enclosures, Installation size: 8, Protection degree: IP55, Bulkhead
GTIN (EAN)	4099987382298	housing, Clamping yoke connection, Standard
Qty.	1 ST	
Type	HDC 24B SS 1M40G ATEX	Version
Order No.	<a href="#">3139880000</a>	HDC enclosures, Installation size: 8, Protection degree: IP55, Base
GTIN (EAN)	4099987382243	housing, Clamping yoke connection, Standard, Size of cable entries:
Qty.	1 ST	M 40
Type	HDC 24B SS 2M40G ATEX	Version
Order No.	<a href="#">3139890000</a>	HDC enclosures, Installation size: 8, Protection degree: IP55, Base
GTIN (EAN)	4099987382250	housing, Clamping yoke connection, Standard, Size of cable entries:
Qty.	1 ST	M 40
Type	HDC 24B TOS 1M32G ATEX	Version
Order No.	<a href="#">3140010000</a>	HDC enclosures, Installation size: 8, Protection degree: IP55, Plug
GTIN (EAN)	4099987382373	housing, Clamping yoke connection, Standard
Qty.	1 ST	

## HDC HDD 48 MC EX 1500

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	HDC 24B TOS 2M32G ATEX	Version
Order No.	<a href="#">3140020000</a>	HDC enclosures, Installation size: 8, Protection degree: IP55, Plug
GTIN (EAN)	4099987382380	housing, Clamping yoke connection, Standard
Qty.	1 ST	
Type	HDC 24B TSS 1M32G ATEX	Version
Order No.	<a href="#">3140030000</a>	HDC enclosures, Installation size: 8, Protection degree: IP55, Plug
GTIN (EAN)	4099987382397	housing, Clamping yoke connection, Standard
Qty.	1 ST	
Type	HDC 24B TSS 1M40G ATEX	Version
Order No.	<a href="#">3140040000</a>	HDC enclosures, Installation size: 8, Protection degree: IP55, Plug
GTIN (EAN)	4099987382403	housing, Clamping yoke connection, Standard, Size of cable entries: M 40
Qty.	1 ST	

## Crimp contacts HD



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

## General ordering data

Type	HDC-C-HD-SM0.14-0.37AG	Version
Order No.	<a href="#">1651520000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190400194	Conductor cross-section, max.: 0.37, turned, Copper alloy
Qty.	100 ST	
Type	HDC-C-HD-SM0.14-0.37AU	Version
Order No.	<a href="#">1651620000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190400293	Conductor cross-section, max.: 0.37, turned, Copper alloy
Qty.	100 ST	
Type	HDC-C-HD-SM0.5AG	Version
Order No.	<a href="#">1651530000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190400200	Conductor cross-section, max.: 0.5, turned, Copper alloy
Qty.	100 ST	
Type	HDC-C-HD-SM0.5AU	Version
Order No.	<a href="#">1651630000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190400309	Conductor cross-section, max.: 0.5, turned, Copper alloy
Qty.	100 ST	
Type	HDC-C-HD-SM0.75-1.00AG	Version
Order No.	<a href="#">1601750000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190134280	Conductor cross-section, max.: 1, turned, Copper alloy
Qty.	100 ST	
Type	HDC-C-HD-SM0.75-1.00AU	Version
Order No.	<a href="#">1651640000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190400316	Conductor cross-section, max.: 1, turned, Copper alloy
Qty.	100 ST	

**HDC HDD 48 MC EX 1500**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories**

Type	HDC-C-HD-SM1.5AG	Version
Order No.	<a href="#">1651550000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190400224	Conductor cross-section, max.: 1.5, turned, Copper alloy
Qty.	100 ST	
Type	HDC-C-HD-SM1.5AU	Version
Order No.	<a href="#">1651650000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190400323	Conductor cross-section, max.: 1.5, turned, Copper alloy
Qty.	100 ST	
Type	HDC-C-HD-SM2.5AG	Version
Order No.	<a href="#">1651560000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190400231	Conductor cross-section, max.: 2.5, turned, Copper alloy
Qty.	100 ST	
Type	HDC-C-HD-SM2.5AU	Version
Order No.	<a href="#">1651660000</a>	Heavy-duty connectors, Crimp contact, HD, HDD, HQ, MixMate, Male,
GTIN (EAN)	4008190400330	Conductor cross-section, max.: 2.5, turned, Copper alloy
Qty.	100 ST	

**Size 8**

The HDD series with machined crimp contacts is designed for high pole counts in tight spaces. Users save installation space with the smaller design, without having to limit the number of poles.

The wire connection level is designed as a crimp contact. The established crimp connection has been used as a standard for decades. Crimp contacts are not delivered with the inserts.

Number of poles: 108

Rated current: 10 A

Rated voltage: 250 V

Nominal voltage acc. to UL/CSA: 600 V AC/DC

**General ordering data**

Type	HDC HDD 108 FC	Version
Order No.	<a href="#">1651220000</a>	HDC insert, Female, 250 V, 10 A, Number of poles: 108, Crimp
GTIN (EAN)	4008190299828	connection, Installation size: 8
Qty.	1 ST	
Type	HDC HDD 48 FC EX 1500	Version
Order No.	<a href="#">3116690000</a>	HDC insert, Female, 1500 V, Number of poles: 48, Crimp connection,
GTIN (EAN)	4099987235914	Installation size: 8
Qty.	1 ST	