

**HDC-KIT-HA 03.301 M P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The PUSH IN connection is a direct-insert method of connection. The preprocessed wire can be inserted directly into the wire connection without the need for any tools.

**General ordering data**

Version	RockStar® , HA, Installation size: 1, PUSH IN, 230 V, 10 A, Plastic, M 20
Order No.	<a href="#">3123920000</a>
Type	HDC-KIT-HA 03.301 M P
GTIN (EAN)	409998727255 1
Qty.	1 items

**HDC-KIT-HA 03.301 M P**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

Net weight 99 g

**Temperatures**

Limit temperature -40 °C ... 100 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC Potassium perfluorobutane sulfonate 29420-49-3

**General data**

Surface finish	Powder coating	Protection degree	IP65
Series	HA		

**Version**

Size of cable entries	M 20	Number of cable entry on top	1
Number of cable entry sideways	0	Type of connection	PUSH IN
Design of locking system	Side-locking clamp on lower side	Installation size	1
Sealing	NBR	Colour (RAL)	RAL 7035
BG	1		

**General data**

Number of poles	3	Connection type PE	PUSH IN connection
Installation size	1	Cable gland	M 20
Basic material	Plastic	Series	HA
Rated voltage (DIN EN 61984)	230 V	Rated current (DIN EN 61984)	10 A
BG	1		

**Version**

Type of connection	PUSH IN	Installation size	1
Conductor cross-section, max.	2.5 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Surface finish	Powder coating	Max. torque for main contact	0.55 Nm
Basic material	Plastic	Min. torque for main contact	0.5 Nm
BG	1		

**Classifications**

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		