


**HDC HA 10 MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



PUSH IN connection technology is a direct plug-in technology. The pre-treated conductor can be plugged directly into the conductor connection level without additional aids.

Number of poles: 4 - 48

Rated current: 10 A

Rated voltage 400 V

Nominal voltage acc. to UL/CSA: 600 V AC/DC

PUSH IN technology

**General ordering data**

Version	, Male, 250 V, 16 A, Number of poles: 10, PUSH IN with actuator, Installation size: 2
Order No.	<a href="#">3124530000</a>
Type	HDC HA 10 MP
GTIN (EAN)	4099987277525
Qty.	1 items

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E92202
Certificate No. (cURus)	E310075

Dimensions and weights

Depth	14.6 mm	Depth (inches)	0.5748 inch
Height	35 mm	Height (inches)	1.378 inch
Width	23 mm	Width (inches)	0.9055 inch
Length	55.4 mm	Length (inches)	2.1811 inch
Net weight	12.78 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Chemical resistance	Substance	Acetone
	Chemical resistance	Resistant
	Substance	Ammonia, watery
	Chemical resistance	Conditionally resistant
	Substance	Petrol
	Chemical resistance	Resistant
	Substance	Benzene
	Chemical resistance	Resistant
	Substance	Diesel oil
	Chemical resistance	Conditionally resistant
	Substance	Acetic acid, concentrated
	Chemical resistance	Resistant
	Substance	Potassium hydroxide
	Chemical resistance	Conditionally resistant
	Substance	Methanol
	Chemical resistance	Conditionally resistant
	Substance	Motor oil
	Chemical resistance	Conditionally resistant
	Substance	Lye, diluted
	Chemical resistance	Resistant
Substance	Hydrochlorofluorocarbons	
Chemical resistance	Conditionally resistant	
Substance	Outdoor use	
Chemical resistance	Conditionally resistant	

Dimensions

Width	23 mm	Total length base	55.4 mm
-------	-------	-------------------	---------

## HDC HA 10 MP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## General data

Number of poles	10	Plugging cycles, silver	≥ 500
Plugging cycles, gold	≥ 500	Plugging cycles, tin	≥ 500
Type of connection	PUSH IN with actuator	Installation size	2
UL 94 flammability rating	V-0	Colour	Light Grey
Insulating material	PC	Tightening torque, max. PE connection	1 Nm
Plugging cycles	≥ 500	Type	Male
Surge voltage category	III	Pollution severity	3
Tightening torque, min. PE connection	0.5 Nm	Basic material	Polycarbonate
Series	HA	Rated voltage (DIN EN 61984)	250 V
Rated impulse voltage (DIN EN 61984)	4 kV	Rated current (DIN EN 61984)	16 A
Free from halogens	false	BG	2
Number of signal contacts	0	Number of power contacts	10
Protection degree	IP20		

## Connection data PE

Connection type PE	PUSH IN connection	Tightening torque, max. PE connection	1 Nm
Tightening torque, min. PE connection	0.5 Nm		

## Power contact

Tightening torque, power contact, max.	1 Nm	
Tightening torque, power contact, min.	0.7 Nm	
Rated voltage (DIN EN 61984), power contact	250 V	
Tightening torque, max. according to the conductor cross-section	Conductor cross-section, min.	0.14 mm <sup>2</sup>
	Conductor cross-section, max.	2.5 mm <sup>2</sup>
	Tightening torque, max.	1 Nm
Stripping length according to the cable diameter	Stripping length	8.00 mm

## Signal contact

Rated impulse voltage (DIN EN 61984), 4 kV signal



## Version

Wire connection cross section AWG, max.	AWG 26	Stripping length, rated connection	8 mm
Type of connection	PUSH IN with actuator	Installation size	2
Wire connection cross section AWG, min.	AWG 14	Conductor cross-section, max.	0.14 mm <sup>2</sup>
Conductor cross-section, min.	2.5 mm <sup>2</sup>	Basic material	Polycarbonate
BG	2		

## Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		

Drawings



**DSTV**

Various accessories are available for our inserts. This includes coding elements for the inserts.

**General ordering data**

Type	DSTV COST4	Version
Order No.	<a href="#">1471300000</a>	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190017354	
Qty.	100 ST	
Type	DSTV COBU5	Version
Order No.	<a href="#">1471500000</a>	Heavy-duty connectors, Accessories, Coding element
GTIN (EAN)	4008190178543	
Qty.	100 ST	