

**SAIBWP-P-5A-4/8-P12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

**General ordering data**

Version	Field attachable connector, M12 Push-Pull
Order No.	<a href="#">3153360000</a>
Type	SAIBWP-P-5A-4/8-P12
GTIN (EAN)	4099987636230
Qty.	1 items

**SAIBWP-P-5A-4/8-P12**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Width	49 mm	Width (inches)	1.9291 inch
Diameter	18.6 mm	Net weight	25 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Technical data customisable plug-in connectors**

Number of poles	5		
Coding	A-coded		
Contact surface	Ni/Au		
Type of connection	PUSH IN		
Housing main material	PA 66		
Insulation resistance	≥ 100 MΩ		
Cable diameter, max.	8 mm		
Cable diameter, min.	3 mm		
Contact material	CuSn		
Conductor cross-section, max.	0.75 mm <sup>2</sup>		
Conductor cross-section, min.	0.14 mm <sup>2</sup>		
Nominal current	4 A		
Protection degree	IP65, IP67		
Plugging cycles	≥ 100		
Pollution severity	3		
Gender of contact	Female		
Rated voltage	Rated voltage	48 V	
	Voltage type	AC	
	Rated voltage	60 V	
	Voltage type	DC	
Shield connection	No		
Threaded ring material	Diecast zinc		
Temperature range of housing	-40 ... +85 ° C		

**General Info**

Number of poles	5	Connection 1	M12
Connection 2	PUSH IN	UL 94 flammability rating	V-0
Housing main material	PA 66	Connection thread	M12 Push-Pull
Contact material	CuSn	Contact surface	Ni/Au
Wire cross-section, solid, min. (AWG)	AWG 26	Wire cross-section, solid, max. (AWG)	AWG 18
Wire connection cross section, finely stranded, min.	0.14 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	0.75 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.08 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	0.5 mm <sup>2</sup>
Wire cross-section, solid, min.	0.14 mm <sup>2</sup>	Wire cross-section, solid, max.	0.75 mm <sup>2</sup>
Contact holder materials	PA	Shielding	No
Protection degree	IP65, IP67	Plugging cycles	≥ 100

## SAIBWP-P-5A-4/8-P12

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Standards

Connector standard	IEC 61076-2-010, IEC 61076-2-101
--------------------	----------------------------------

### Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

**Dimensioned drawing**



**Pole scheme**



**SAIBWP-P-5A-4/8-P12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

