

**TCB INL BIG 1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Inspired by 5S and lean management methods, Weidmüller foam inserts ensure an efficient and tidy workplace. Designed according to a modular principle, they offer many advantages and can be selected according to individual requirements.

**General ordering data**

Order No.	3155550000
Type	<a href="#">TCB INL BIG 1</a>
GTIN (EAN)	4099987654944
Qty.	1 items

**Technical data****Dimensions and weights**

Depth	50 mm	Depth (inches)	1.9685 inch
Height	390 mm	Height (inches)	15.3543 inch
Width	560 mm	Width (inches)	22.0472 inch
Diameter	0 mm	Net weight	3015.9 g

**Technical data**

Description of article	Foam inlay universal big
------------------------	--------------------------

**Tool chest**

Assembly	with tools
----------	------------

**Assortments**

Diameter	0 mm
----------	------

**Classifications**

ETIM 8.0	EC011819	ETIM 9.0	EC011819
ETIM 10.0	EC011819	ECLASS 14.0	21-07-04-12
ECLASS 15.0	21-07-04-12		

## TCB INL BIG 1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## DMS PRO



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

## General ordering data

Type	AKKU DMS PRO	Version	
Order No.	<a href="#">1479110000</a>	Mounting tool	
GTIN (EAN)	4050118348712		
Qty.	1 ST		

## Tools



Sheathing stripper for PVC cables

## General ordering data

Type	AM 16	Version	
Order No.	<a href="#">9204190000</a>	Tools, Sheathing strippers	
GTIN (EAN)	4032248608133		
Qty.	1 ST		

## BE6.3 bits - slotted

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
 Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126



## General ordering data

Type	BIT E6.3 0.4X2,5X70	Version	
Order No.	<a href="#">2748900000</a>	Screwdriver insert, Blade width (B): 2.5 mm, Blade length: 70 mm,	
GTIN (EAN)	4050118894776	Blade thickness (A): 0.4 mm	
Qty.	5 ST		

## TCB INL BIG 1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	BIT E6,3 0,6X3,5X70	Version
Order No.	<a href="#">2748920000</a>	Screwdriver insert, Blade width (B): 3.5 mm, Blade length: 70 mm,
GTIN (EAN)	4050118894790	Blade thickness (A): 0.6 mm
Qty.	5 ST	
Type	BIT E6,3 1,0X5,5X70	Version
Order No.	<a href="#">2748940000</a>	Screwdriver insert, Blade width (B): 5.5 mm, Blade length: 70 mm,
GTIN (EAN)	4050118894813	Blade thickness (A): 1 mm
Qty.	5 ST	

### E6.3 bits - Pozidriv / Supadriv

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
 Crosshead bits Pozidriv PZ/DIN 5262, 1/4" drive, E 6.3  
 DIN 3126



### General ordering data

Type	BIT E6,3 PZ1X70	Version
Order No.	<a href="#">2748960000</a>	Screwdriver insert, Blade width (B): 1 mm, Blade length: 70 mm,
GTIN (EAN)	4050118895155	Blade thickness (A): 1 mm, Blade size, crosshead: 1
Qty.	5 ST	
Type	BIT E6,3 PZ2X70	Version
Order No.	<a href="#">2748970000</a>	Screwdriver insert, Blade width (B): 2 mm, Blade length: 70 mm,
GTIN (EAN)	4050118895162	Blade thickness (A): 2 mm, Blade size, crosshead: 2
Qty.	5 ST	

## Accessories

### Bits E6,3 - Torx®



The Weidmüller bits are standard bits which are highly popular with users thanks to their good quality, large range and efficiency. The computer-controlled hardening method enables Weidmüller to guarantee a consistently high standard of quality.

The high-quality raw materials used make it possible to reach torques far higher than any of those specified in the relevant DIN standards:

- DIN 5261 for PH/PZ bits,
- DIN 5263 for slotted bits,
- Camcar standard for TORX bits

That means a long life at high torques and hence ideal conditions for standard situations.

The benefits:

- Suitable for all types of screws. Because of their excellent hardness values of 59-61 HRC, they are suitable for use with both manual and power tools.
- Good wearing resistance and thus a long life expectancy.
- Optimum fit in all DIN screws means low wear and optimum torque transmission.
- Manufactured to meet professional quality criteria according to relevant ISO standards with a consistently high standard of quality.

### General ordering data

Type	BIT E6,3 T15 X 70	Version
Order No.	<a href="#">2749000000</a>	Screwdriver insert
GTIN (EAN)	4050118895193	
Qty.	5 ST	
Type	BIT E6,3 T20 X 70	Version
Order No.	<a href="#">2749010000</a>	Screwdriver insert
GTIN (EAN)	4050118895308	
Qty.	5 ST	
Type	BIT E6,3 T40 X 70	Version
Order No.	<a href="#">2749020000</a>	Screwdriver insert
GTIN (EAN)	4050118895315	
Qty.	5 ST	

### Crimping tools



Crimping tools for insulated connectors  
 cable lugs, terminal pins, parallel and serial connectors,  
 plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

## TCB INL BIG 1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## General ordering data

Type	CTI 6	Version	
Order No.	<a href="#">9006120000</a>	Pressing tool, Crimping tool for contacts, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Oval crimping, Double crimp	
GTIN (EAN)	4008190044527		
Qty.	1 ST		

## DMS PRO



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

## General ordering data

Type	DMS PRO	Version	
Order No.	<a href="#">1479120000</a>	Mounting tool	
GTIN (EAN)	4050118287011		
Qty.	1 ST		

## Measuring instruments



Precision tools from Weidmüller are in use worldwide. Weidmüller takes this responsibility seriously and offers comprehensive services. Tools should still function perfectly even after many years of constant use. Weidmüller therefore offers its customers the "Tool Certification" service. This technical testing routine allows Weidmüller to guarantee the proper functioning and quality of its tools.

## General ordering data

Type	FLEXIMET 5 M	Version	
Order No.	<a href="#">2534210000</a>	Measuring tape	
GTIN (EAN)	4050118545975		
Qty.	1 ST		

## TCB INL BIG 1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

## Accessories

www.weidmueller.com

## VDE insulated telephone pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

## General ordering data

Type	FRZ S 200	Version	
Order No.	<a href="#">9046380000</a>	Pliers	
GTIN (EAN)	4032248357697		
Qty.	1 ST		

## Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

## General ordering data

Type	KT 8	Version	
Order No.	<a href="#">9002650000</a>	Cutting tools, Cutting tool for one-hand operation	
GTIN (EAN)	4008190020163		
Qty.	1 ST		

## Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

## TCB INL BIG 1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## General ordering data

Type	PZ 6 ROTO L	Version	
Order No.	<a href="#">1444050000</a>	Pressing tool, Crimping tool for wire-end ferrules, 0.14mm <sup>2</sup> , 6mm <sup>2</sup> ,	
GTIN (EAN)	4050118248593	Trapezoidal crimp	
Qty.	1 ST		

## Angled slotted screwdriver



## General ordering data

Type	SD TO 0,6X3,0	Version	
Order No.	<a href="#">2749560000</a>	Screwdriver, Blade width (B): 3 mm, Blade length: 70 mm, Blade	
GTIN (EAN)	4050118895889	thickness (A): 0.6 mm	
Qty.	1 ST		

## Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

## General ordering data

Type	STRIPAX	Version	
Order No.	<a href="#">9005000000</a>	Tools, Stripping and cutting tool	
GTIN (EAN)	4008190072506		
Qty.	1 ST		

## TCB INL BIG 1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Electronic diagonal-cutting pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

## General ordering data

Type	SUPER CUT	Version	
Order No.	<a href="#">9205150000</a>	Pliers	
GTIN (EAN)	4032248698950		
Qty.	1 ST		

## Combined screwing and cutting tool "Swifty® CS"

Combined cutting/stripping tool Swifty® CS and Swifty® CS set for crimp-free cutting and stripping of copper cables up to 1.5 mm<sup>2</sup> solid and 2.5 mm<sup>2</sup> flexible.

## General ordering data

Type	SWIFTY CS SET	Version	
Order No.	<a href="#">9006060000</a>	Cutting and screwing-tool, Cutting tool for one-hand operation	
GTIN (EAN)	4032248257638		
Qty.	1 ST		