

**HDC MHP 200 MC 2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

**General ordering data**

Version	Module, 1000 V, 200 A, Number of poles: 1, Crimp connection, Male, Required plug-in slots: 2
Order No.	<a href="#">3157260000</a>
Type	HDC MHP 200 MC 2
GTIN (EAN)	4099987663489
Qty.	1 items

## HDC MHP 200 MC 2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	60.3 mm	Height (inches)	2.374 inch
Width	34 mm	Width (inches)	1.3386 inch
Net weight	21 g		

### Temperatures

Limit temperature -40 °C ... 125 °C

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

### General data

Number of poles	1	UL 94 flammability rating	V-0
Insulation resistance	10 <sup>12</sup> Ω	Plugging cycles	≥ 500
Type	Male	Surge voltage category	III
Pollution severity	3	Basic material	Polycarbonate, glass fibre reinforced
Series	ModuPlug	Rated voltage (DIN EN 61984)	1000 V
Rated voltage according to UL/CSA	600 V	Rated impulse voltage (DIN EN 61984)	8 kV
Rated current (DIN EN 61984)	200 A	Required plug-in slots	2

### PE connection data

Connection type PE Screw connection via module frame

### Version

Stripping length, rated connection	19 mm	Type of connection	Crimp connection
Conductor cross-section, max.	70 mm <sup>2</sup>	Conductor cross-section, min.	25 mm <sup>2</sup>

### Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-17
ECLASS 15.0	27-44-02-17		

