

**HDC 40D TOBU 1M32 BP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Plastic enclosures are particularly suitable for applications where the resistance of metals is not sufficient. In addition, the enclosures shown here are lighter and slightly cheaper than standard aluminum enclosures. It can therefore make sense to use plastic enclosures in applications where the materials do not need to be as robust. The tightness is still IP65.

**General ordering data**

|            |  |
|------------|--|
| Version    | HDC enclosures, Installation size: 6, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32, M 40 |
| Order No.  | <a href="#">3164310000</a>   |
| Type       | HDC 40D TOBU 1M32 BP   |
| GTIN (EAN) | 4099987800181  |
| Qty.       | 1 items  |

## HDC 40D TOBU 1M32 BP

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 94 mm   | Depth (inches)  | 3.7008 inch |
| Height     | 99.5 mm | Height (inches) | 3.9173 inch |
| Width      | 56 mm   | Width (inches)  | 2.2047 inch |
| Net weight | 175 g   |                 |             |

## Temperatures

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Dimensions

|                     |           |                      |       |
|---------------------|-----------|----------------------|-------|
| Cable entry         | w. thread | Total length housing | 94 mm |
| Height of housing B | 76.5 mm   |                      |       |

## General data

|                           |                            |                |           |
|---------------------------|----------------------------|----------------|-----------|
| UL 94 flammability rating | V-0                        | Surface finish | untreated |
| Protection degree         | IP65, in plugged condition |                |           |

## Version

|                                |                                  |                              |                                    |
|--------------------------------|----------------------------------|------------------------------|------------------------------------|
| Size of cable entries          | M 32, M 40                       | Top part/bottom part/lid     | upper part                         |
| Cover                          | without cover                    | Number of cable entry on top | 1                                  |
| Number of cable entry sideways | 0                                | Design of housing            | Cable entry from top, Plug housing |
| Design of locking system       | Side-locking clamp on lower side | Design                       | high                               |
| Installation size              | 6                                | Cable entry                  | w. thread                          |
| Type                           | Plug                             | Clamp version                | Side-locking clamp                 |
| Sealing                        | no sealing                       | Internal thread              | M 32                               |
| Colour (RAL)                   | RAL 9011                         | BG                           | 6                                  |
| Suitable for ModuPlug®         | Yes                              |                              |                                    |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000437    | ETIM 9.0    | EC000437    |
| ETIM 10.0   | EC000437    | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 |             |             |

**HDC 40D TOBU 1M32 BP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## HDC 40D TOBU 1M32 BP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Bulkhead housing



Plastic enclosures are particularly suitable for applications where the resistance of metals is not sufficient. In addition, the enclosures shown here are lighter and slightly cheaper than standard aluminum enclosures. It can therefore make sense to use plastic enclosures in applications where the materials do not need to be as robust. The tightness is still IP65.

#### General ordering data

|            |                            |         |  |
|------------|----------------------------|---------|--|
| Type       | HDC 16B ABU BP             | Version |  |
| Order No.  | <a href="#">3107150000</a> |         | HDC enclosures, Installation size: 6, Protection degree: IP65, in plugged condition, Bulkhead housing, Side-locking clamp on lower side, Side-locking clamp not replaceable, Standard, Size of cable entries: none |
| GTIN (EAN) | 4099987 172028             |         |  |
| Qty.       | 1 ST                       |         |  |

### Base housing



Plastic enclosures are particularly suitable for applications where the resistance of metals is not sufficient. In addition, the enclosures shown here are lighter and slightly cheaper than standard aluminum enclosures. It can therefore make sense to use plastic enclosures in applications where the materials do not need to be as robust. The tightness is still IP65.

#### General ordering data

|            |                            |         |   |
|------------|----------------------------|---------|---|
| Type       | HDC 16B SBU 1M32 BP        | Version |   |
| Order No.  | <a href="#">3164410000</a> |         | HDC enclosures, Installation size: 6, Protection degree: IP65, in plugged condition, Base housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 32, M 40        |
| GTIN (EAN) | 4099987800686              |         |   |
| Qty.       | 1 ST                       |         |   |
| Type       | HDC 16B SBU 2M32 BP        | Version |   |
| Order No.  | <a href="#">3164420000</a> |         | HDC enclosures, Installation size: 6, Protection degree: IP65, in plugged condition, Base housing, Side-locking clamp on lower side, Standard, Size of cable entries: 2*M32, M 32, M 40 |
| GTIN (EAN) | 4099987800709              |         |   |
| Qty.       | 1 ST                       |         |   |

### Size 4



The PUSH IN connection is a direct-insert method of connection. The preprocessed wire can be inserted directly into the wire connection without the need for any tools.

Number of poles: 10

Rated current: 16 A

Rated voltage: 500 V

Nominal voltage acc. to UL/CSA: 600 V AC/DC

## HDC 40D TOBU 1M32 BP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC HE 10 FP               | Version  |
| Order No.  | <a href="#">1873540000</a> | HDC insert, Female, 500 V, 16 A, Number of poles: 10, PUSH IN, |
| GTIN (EAN) | 4032248458158              | Installation size: 4   |
| Qty.       | 1 ST                       |  |
| Type       | HDC HE 10 MP               | Version  |
| Order No.  | <a href="#">1873550000</a> | HDC insert, Male, 500 V, 16 A, Number of poles: 10, PUSH IN,   |
| GTIN (EAN) | 4032248458165              | Installation size: 4   |
| Qty.       | 1 ST                       |  |

### IP68 version



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications. The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure. Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | VG M32-1/K68               | Version   |
| Order No.  | <a href="#">1909880000</a> | VG K (standard plastic cable gland), Cable glands, straight, M 32, 10 |
| GTIN (EAN) | 4032248536801              | mm, OD min. 15 - OD max. 21 mm, IP54, IP66, IP67, IP68 - 5 bar (30    |
| Qty.       | 20 ST                      | min.), Polyamide 6  |