


**PF RS 100 OR 2000MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The RS 100 Profi offers you a flexible solution for your mounting needs, as both DIN rail mounting and wall mounting are possible. This versatility facilitates integration into different environments and applications. The housing can be used for the Eurocard PCB standard. The profile can be cut to size so that you can adapt it precisely to your specific requirements. For particularly heavy components, additional locking feet can be used to improve stability and thus increase the safety of your installation.

Another practical feature is the option of using a cover profile to protect large components.

**General ordering data**

Version	Profile housing, RS 100 orange, Extruded profile, Width: 2000 mm
Order No.	<a href="#">4144870000</a>
Type	PF RS 100 OR 2000MM
GTIN (EAN)	4008190377410
Qty.	2 M

## PF RS 100 OR 2000MM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	19 mm	Depth (inches)	0.748 inch
Height	104 mm	Height (inches)	4.0945 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	406.25 g		

## Temperatures

Operating temperature	-50 °C...60 °C
-----------------------	----------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

UL 94 flammability rating	V-0	Insulating material	PVC
Surface finish	untreated	Basic material	PVC

## General data

Colour	orange	Protection degree	IP20 in installed state
Colour chart (similar)	RAL 2000	Encapsulation option	No

## Important note

Product information	<p>3 heights are available for the cover profile and the end plates:  TS mounting without cover: TS 32 = 45 mm, TS35x7.5 = 40.5 mm  TS mounting with low cover: TS 32 = 89 mm, TS 35x7.5 = 84.5 mm  TS mounting with high cover: TS 32 = 121 mm, TS 35x7.5 = 116.5 mm  Direct mounting, without/low/high cover: 24 / 69 / 99 mm  Dimensions of the PCB  Thickness: 1.6 (±0.2) mm, width: 100 (+0.5) mm  Dimension of the RS section = length of the printed circuit board - 4.5 mm  Dimension of ADP section = PCB length - 1 mm  Example:  PCB length 160 mm, RS = 155.5 mm, ADP = 159 mm"</p>
---------------------	---

## Classifications

ETIM 7.0	EC002779	ETIM 8.0	EC002779
ETIM 9.0	EC002779	ETIM 10.0	EC002779
ECLASS 11.0	27-18-27-92	ECLASS 12.0	27-18-27-92
ECLASS 13.0	27-19-06-01	ECLASS 14.0	27-19-06-01
ECLASS 15.0	27-19-06-01		

## Drawings

