PCF CROSSLINK 5MM PITCH



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com



Large potential for small terminals.

For efficient electrical distribution directly at the connection:

- Isolated comb rail
- Available with the most standard pole numbers
- Easy to shorten

Simply reduce in size to match the number of poles and connect with the conductor in a single working procedure.

For retrofitting or deliberate reduction of the thermal load on the PCB.

General ordering data

Version	Printed circuit board terminals, Accessories, Cross- connector, Number of poles: 2	
Order No.	<u>6382680000</u>	
Туре	PCF CROSSLINK 5MM PITCH	
GTIN (EAN)	4008190549541	
Qty.	1000 items	
Product data		
Packaging	Вох	

Catalogue status / Drawings







Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals					
ROHS	Conform				
Dimensions and weights					
Net weight	1.04 g				
Environmental Product Comp					
RoHS Compliance Status REACH SVHC	Compliant without exemption No SVHC above 0.1 wt%				
System parameters					
Pitch in mm (P)	5.00 mm	Pitch in inches (P)	0.197 "		
Number of poles	2	Pin series quantity	1		
L1 in inches	0.197 "	Protection degree	IP20		
Material data					
Contact material	Cu-alloy	Storage temperature, min.	-40 °C		
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C		
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C		
Temperature range, installation, max.	100 °C				
Conductors suitable for conn	ection		,		
Reference text	Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P)				
Rated data acc. to IEC					
tested acc. to standard	IEC 60664-1, IEC 61984				
Packing					
Packaging	Box	VPE length	215.00 mm		
VPE width	136.00 mm	VPE height	54.00 mm		
Important note					
IPC conformity	recognized standards and no	e developed, manufactured and delivered orms and comply with the assured prope n accordance with IPC-A-610 "Class 2". F	rties in the data sheet resp.		
Notes	 Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months 				
Classifications					
ETIM 6.0	EC002848	ETIM 7.0	EC002848		
ETIM 8.0	EC002848	ETIM 9.0	EC002848		

Creation date 07.11.2025 09:44:56 MEZ

Catalogue status / Drawings 2







Weidmüller Interface GmbH & Co. KG

3

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

ETIM 10.0	EC002848	ECLASS 9.0	27-44-04-92
ECLASS 9.1	27-44-04-92	ECLASS 10.0	27-44-04-92
ECLASS 11.0	27-46-04-06	ECLASS 12.0	27-46-04-06
ECLASS 13.0	27-46-04-06	ECLASS 14.0	27-46-04-06
ECLASS 15.0	27-46-04-06		