


IE-SFP-F-1310-MM2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller's new industrial Ethernet active products include DIN-rail (Wall) mounting unmanaged, managed switches and media converters, as well as modular rack managed switches. With outstanding performances, the new IE products will offer you an overall one-stop solution to your industrial networks.

General ordering data

Version	Active industrial Ethernet,Accessories
Order No.	7760048159
Type	IE-SFP-F-1310-MM2
GTIN (EAN)	6944169652134
Qty.	1 items
Delivery status	Discontinued
Local product	Only available in certain countries

IE-SFP-F-1310-MM2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General ordering data

Local product	Only available in certain countries
---------------	-------------------------------------

Dimensions and weights

Height	8.5	Height (inches)	0.3346 inch
Width	13.7	Width (inches)	0.5394 inch
Length	57.2 mm	Length (inches)	2.252 inch
Net weight	40 g		

Temperatures

Storage temperature	-40 °C...+85 °C	Operating temperature	-40 °C...+85 °C
Humidity	5...95 %, no condensation		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Approvals

According to	SFP MSA(INF-8074i), IEEE802.3ah	EMI	FCC Part 15 Class B, EN 55022 Class B(CISPR 22B), VCCI Class B
EMS	IEC 61000-4-2 CR-1089-CORE, IEC 61000-4-3, MIL-STD-883E Method 3015.7 Class 1(>1.5KV), FDA 21CFR 1040.10 and 1040.11, EN 60950, EN (IEC) 60825-1,2	Approvals	RoHS

Environmental conditions

Humidity	5...95 %, no condensation
----------	---------------------------

Fibre optic Fast Ethernet

Wavelength Fast Ethernet	1310 nm	Max. TX Fast Ethernet	-14 dBm
Min. TX Fast Ethernet	-20 dBm	Receive sensitivity Fast Ethernet	-31 dBm
Typical distances Fast Ethernet	0 - 2 km (multi-mode fibre optic cable)	Saturation-Fast Ethernet	-8.00 dBm

Guarantee

Time interval	3 years
---------------	---------

Technical data

Protection degree	IP20
-------------------	------

Classifications

ETIM 9.0	EC001121	ETIM 10.0	EC001121
ECLASS 14.0	27-44-03-92	ECLASS 15.0	27-44-03-92