



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

| | |
|------------|---|
| Version | Cable ties, 7.8 x 240 mm, Polyamide 66, 540 N |
| Order No. | 7940006066 |
| Type | CB 240/7,8 NC |
| GTIN (EAN) | 4032248520190 |
| Qty. | 2500 items |

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E317499 |

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 1.7 mm | Depth (inches) | 0.0669 inch |
| Height | 240 mm | Height (inches) | 9.4488 inch |
| Width | 7.8 mm | Width (inches) | 0.3071 inch |
| Net weight | 3.55 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...85 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Installation materials

| | | | |
|-----------------------------------|---------|-----------------------------------|--------------|
| UV-resistant | No | For re-opening | No |
| UL 94 flammability rating | V-2 | Operating temperature range, max. | 85 °C |
| Operating temperature range, min. | -40 °C | Halogen | No |
| Cable diameter, max. | 63 mm | Basic material | Polyamide 66 |
| Tensile strength | 540 N | Bundle diameter, max. | 63 mm |
| Tensile strength (Pound-force) | 121 lbf | Bundle diameter, min. | 3.5 mm |

Important note

| | |
|---------------------|--|
| Product information | Number of bags in box (pieces): 25 Number of items in bag (pieces): 100 One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered. |
|---------------------|--|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000046 | ETIM 9.0 | EC000046 |
| ETIM 10.0 | EC000046 | ECLASS 14.0 | 27-14-07-02 |
| ECLASS 15.0 | 27-14-07-02 | | |

Drawings

