

FAD 1771-WF SL18 M US

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

Adapters for migration – PLC-5.

The front adapters with pre-assembled cables provide a safe migration from the PLC-5 cards to other PLC/DCS systems or the u-remote modules from Weidmüller.

General ordering data

| | |
|------------|---------------------------------------|
| Order No. | 7940125451 |
| Type | FAD 1771-WF SL18 M US |
| GTIN (EAN) | 4064675209195 |
| Qty. | 1 items |

FAD 1771-WF SL18 M US

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

| | | | |
|------------|------------|-----------------|--------------|
| Depth | 53 mm | Depth (inches) | 2.0866 inch |
| Height | 269 mm | Height (inches) | 10.5905 inch |
| Width | 32 mm | Width (inches) | 1.2598 inch |
| Net weight | 13217.17 g | | |

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -40...60 °C | Operating temperature | -25...50 °C |
|---------------------|-------------|-----------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Connection data

| | |
|-------------------|------------------------|
| Connection to PLC | SL 3.5/F 18p connector |
|-------------------|------------------------|

Ratings data

| | | | |
|--------------------------|-----|-------------------------|-----|
| Max. current per channel | 2 A | Total operating current | 6 A |
|--------------------------|-----|-------------------------|-----|

Insulation coordination (EN50178)

| | | | |
|----------------------------|--------------|--------------------------|------------|
| According to | DIN EN 50178 | Rated insulation voltage | < 250 V AC |
| Surge voltage category | II | Pollution severity level | 2 |
| Insulation test voltage AC | 1.2 kV | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002584 | ETIM 9.0 | EC002584 |
| ETIM 10.0 | EC002584 | ECLASS 14.0 | 27-33-02-92 |
| ECLASS 15.0 | 27-33-02-92 | | |

FAD 1771-WF SL18 M US

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

