

KEBXHS604020S4B1 AK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Klippon® EBx HS stainless steel enclosures, where the lid is fixed by Hinge and Screws, are offered as high quality products with leading performance characteristics in oil and chemistry hazardous industry. It is certified and complied with the international standards - like ATEX and IECEx approval.

General ordering data

Version	Klippon EBx HS (Essential Box Ex - Hinge Screw), Empty enclosure, Height: 600 mm, Width: 400 mm, Depth: 200 mm, Gland plates: Bottom, Basic material: Stainless steel 1.4404 (316L), Brushed, silver
Order No.	8000071029
Type	KEBXHS604020S4B1 AK
GTIN (EAN)	4064675385066
Qty.	1 items
Local product	Only available in certain countries

KEBXHS604020S4B1 AK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

General ordering data

Local product

Only available in certain countries

Dimensions and weights

Depth	200 mm	Depth (inches)	7.874 inch
Height	600 mm	Height (inches)	23.622 inch
Width	400 mm	Width (inches)	15.748 inch
Mounting dimension - height	560 mm	Mounting dimension - width	360 mm
Net weight	12865 g		

Temperatures

Operating temperature -55 °C...135 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Cable glands, left

M63	3	M75	3
M12	180	M50	8
M16	87	M32	21
M25	36	M20	58
M40	11		

Cable glands, right

M25	36	M63	3
M75	3	M16	87
M40	11	M50	8
M32	21	M20	58
M12	180		

Cable glands, top/bottom

M20	46	M12	137
M63	3	M40	11
M32	14	M25	27
M50	4	M75	3
M16	73		

KEBXHS604020S4B1 AK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Certificate numbers enclosure

Declaration of Conformity No. (DoC LVD)	DE PS265X 210819 001ISS01	Attestation of Conformity No. (AoC)	DE PS265x 210819 000ISS01
Certificate no. empty enclosure (INMETRO)	LMP 21.0601U	Certificate no. Terminal Box (ATEX)	IBExU 21ATEX 1017 X
Certificate no. empty enclosure (ATEX)	IBExU 21ATEX 1016 U	Certificate no. Terminal Box (INMETRO)	LMP 21.0602X
Certificate no. Terminal Box (IECEX)	IECEX IBE 21.0012	Certificate no. empty enclosure (IECEX)	IECEX IBE 21.0006U
Approval conditions	ATEX, IECEX, INMETRO		

General information

Material thickness of cover	1.5 mm	Material thickness of flange	3 mm
Material thickness	1.5 mm	Operating temperature, max.	135 °C
Operating temperature, min.	-55 °C	Lid attachment	M6 hex-head slotted screws SW10 + hinges
Standards	EN 60079-0, IEC 60079-0, EN 60079-7, IEC 60079-7, EN 60079-11, IEC 60079-11, EN 60079-31, IEC 60079-31	Surface finish	Brushed
Impact resistance	7 J ATEX version, 10 J version standard	AF size	10 mm
Protection degree	IP66	Basic material	Stainless steel 1.4404 (316L)
Seal material	Silicone (cover + flange)	Torque for lid screws	2.5 Nm
Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread	Enclosure attachment	4 or 6, M6 blind thread hole on backside; optionally via additional mounting feet
Flange plate mounting	M6 hexagonal head screws 10 SW	Protection class (UL)	Type 1, Type 4, Type 4X
Number of lid screws	3	Gland plates	Bottom
Access opening: width	343.6 mm	Opening angle lid	125.00 °
Flange plate	Yes	Max. payload	24 kg
Lid	Yes	Access opening: height	549.6 mm
Position PE bolts	Enclosure side C	Areas of use	Chemical industry, Explosive risk zone, Oil and gas industry, Onshore, Process industry, Building systems and technology, Machine construction, Packaging industry

Housing earth

Earth, enclosure, internal	Welded-on M6 stainless-steel earth stud in enclosure body and lid.
----------------------------	--

horizontal assembly

Number of DIN rails and terminals (10 mm ² , horizontal)	8x30	Number of DIN rails and terminals (16 mm ² , horizontal)	8x25
Number of DIN rails and terminals (2.5 mm ² , horizontal)	8x61	Number of DIN rails and terminals (35 mm ² , horizontal)	8x18
Number of DIN rails and terminals (4 mm ² , horizontal)	8x51	Number of DIN rails and terminals (6 mm ² , horizontal)	8x38

KEBXHS604020S4B1 AK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

vertical assembly

Number of DIN rails and terminals (10 mm², vertical) 5x49

Number of DIN rails and terminals (2.5 mm², vertical) 5x98

Number of DIN rails and terminals (4 mm², vertical) 5x82

Number of DIN rails and terminals (16 mm², vertical) 5x41

Number of DIN rails and terminals (35 mm², vertical) 5x30

Number of DIN rails and terminals (6 mm², vertical) 5x61

Important note

Product information All articles with M6 threaded rivet as standard; UL variants with M10 earth bolt on request

Classifications

ETIM 8.0 EC002503

ETIM 10.0 EC002503

ECLASS 15.0 27-18-05-02

ETIM 9.0 EC002503

ECLASS 14.0 27-18-05-02

KEBXHS604020S4B1 AK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

