

**PAC-M340-SD37-V0-0M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|            |   |
|------------|---|
| Version    | Pre-assembled cable, PAC, Cable LiYCY, 0.25 mm <sup>2</sup> |
| Order No.  | <a href="#">7789639005</a>                                  |
| Type       | PAC-M340-SD37-V0-0M5  |
| GTIN (EAN) | 4099986632059   |
| Qty.       | 1 items   |

## PAC-M340-SD37-V0-0M5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |       |
|------------|-------|
| Net weight | 220 g |
|------------|-------|

### Temperatures

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

### Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

### General Data

|                     |                      |                       |                           |
|---------------------|----------------------|-----------------------|---------------------------|
| Cable length        | 0.5 m                | Suitable for          | Analogue signals          |
| Basic material      | PVC                  | Cable                 | Cable LiYCY               |
| Interface connector | SUB-D FEMALE 37P     | Number of poles, min. | 37-pole                   |
| Outer diameter      | 12.2 ± 1 mm          | Connector PLC side    | FUJITSU FCN363J040<br>40P |
| Wire cross-section  | 0.25 mm <sup>2</sup> |                       |                           |

### Electrical Data

|   |           |                         |                   |
|---|-----------|-------------------------|-------------------|
| Total current, max.                         | 3 A       | High voltage test       | 1 KV/1s           |
| Permissible current strength per path, max. | 1 A       | Rated voltage           | ≤ 60 Vdc ≤ 25 Vac |
| Resistance                                  | ≤ 80 mΩ/m | Capacity (wire / wires) | 300 pF/m          |
| Capacity (wire / shield)                    | 300 pF/m  |                         |                   |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |