

KTB FS 262615 S2B2 TUBEBOX SAKK 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Junction boxes for antennas and non-safety-related track-side equipment, as well as for the power supply of emergency systems in the tunnel. The junction boxes provide durable protection for electronics in harsh tunnel environments. In addition, depending on the equipment, the enclosures are certified for fire-protection-proof uninterrupted emergency power supply.

General ordering data

Version	Klippon TB FS (Terminal Box - Fixing Screw), Enclosures, Height: 260 mm, Width: 260 mm, Depth: 150 mm, Gland plates: Bottom, top, Basic material: Stainless steel 1.4301 (304), Brushed, silver
Order No.	8000080477
Type	KTB FS 262615 S2B2 TUBEBOX SAKK 10
GTIN (EAN)	4064675593188
Qty.	1 items

KTB FS 262615 S2B2 TUBEBOX SAKK 10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Dimensions and weights

Depth	150 mm	Depth (inches)	5.9055 inch
Height	260 mm	Height (inches)	10.2362 inch
Width	260 mm	Width (inches)	10.2362 inch
Net weight	6989.36 g		

Temperatures

Operating temperature	-60 °C...135 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	64dfc213-93f0-4c79-8ffa-c97fa9dcb873

General information

Material thickness of cover	1.5 mm	Material thickness of flange	3 mm
Material thickness of enclosure	1.5 mm	Operating temperature, max.	135 °C
Operating temperature, min.	-60 °C	UL 94 flammability rating	V-0
Lid attachment	M6 hex-head slotted screws SW10	Standards	EN 60068 ≤1m from the track, EN 45545 HL3
Surface finish	Brushed	Impact resistance	10 J version standard
Protection degree	IP66, IP67	Basic material	Stainless steel 1.4301 (304)
Seal material	Silicone	Protection class (UL)	Type 3, Type 4X, Type 12
Gland plates	Bottom, top	Flange plate	Yes

horizontal assembly

SAKK 10	1x6	Fuse holder available	Yes
---------	-----	-----------------------	-----

vertical assembly

Fuse holder available	Yes
-----------------------	-----

Material data

UL 94 flammability rating	V-0	Surface finish	Brushed
Basic material	Stainless steel 1.4301 (304)		

General data

Colour	silver	Protection degree	IP66, IP67
Colour chart (similar)	RAL 7001		

Housing

Basic material	Stainless steel 1.4301 (304)
Drill holes side A	none
Drill holes side B	none
Reference product	Cardinality 6
	Reference SAKK 10

KTB FS 262615 S2B2 TUBEBOX SAKK 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC000261	ETIM 9.0	EC000261
ETIM 10.0	EC000261	ECLASS 14.0	27-18-01-01
ECLASS 15.0	27-18-01-01		