

LST_CTVT_3PHASEPEATTB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



With our pre-assembled SET's for instrument transformer wiring you save time and storage costs. We offer various application setups including all relevant accessories and including labeling in one complete package.

General ordering data

| | |
|------------|---|
| Version | Test-disconnect terminal, dark beige, blue, Green/yellow, 6 mm ² , 30 A, 500 V, Number of connections: 22, Number of levels: 1 |
| Order No. | 8000082523 |
| Type | LST_CTVT_3PHASEPEATTB |
| GTIN (EAN) | 4064675535614 |
| Qty. | 1 items |

LST_CTVT_3PHASEPEATTB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 79 mm | Depth (inches) | 3.1102 inch |
| Height | 100 mm | Height (inches) | 3.937 inch |
| Width | 105 mm | Width (inches) | 4.1338 inch |
| Net weight | 470 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|--------------------------------|--------|---------------------------|------------------------------------|
| Basic material | Wemid | Colour | dark beige, blue, Green/ yellow |
| Colour of operational elements | orange | UL 94 flammability rating | V-0 |

System specifications

| | | | |
|--------------------------|-----|----------------------|--------------|
| End cover plate required | No | Number of potentials | 4 |
| Number of levels | 1 | Mounting rail | TS 35, TS 32 |
| PE function | Yes | | |

Additional technical data

| | | | |
|------------|--------|------------------|---------|
| Open sides | closed | Type of mounting | Snap-on |
|------------|--------|------------------|---------|

Conductors for clamping (rated connection)

| | | | |
|---|---------------------|---|--------------------|
| Gauge to IEC 60947-1 | A4 | Wire connection cross section AWG, max. | AWG 8 |
| Connection direction | top | Stripping length | 12 mm |
| Number of connections | 22 | Clamping range, max. | 10 mm ² |
| Clamping range, min. | 0.5 mm ² | Blade size | 0.8 x 4.0 mm |
| Wire connection cross section AWG, min. | AWG 22 | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | Wire connection cross section, finely stranded, max. | 10 mm ² |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | Connection cross-section, stranded, max. | 10 mm ² |

LST_CTVT_3PHASEPEATTB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | |
|--|---|---|
| Connection cross-section, stranded, min. 0.5 mm ² | Wire connection cross-section, solid core, max. | 10 mm ² |
| Wire connection cross-section, solid core, min. | 0.5 mm ² | Connection cross-section, finely stranded, min. |
| | | 0.5 mm ² |

General

| | | | |
|---|---------------|---|--------------|
| Wire connection cross section AWG, max. | AWG 8 | Wire connection cross section AWG, min. | AWG 22 |
| Standards | IEC 60947-7-1 | Mounting rail | TS 35, TS 32 |

Rating data

| | | | |
|---------------------------------|-------------------|------------------------|---------------|
| Rated cross-section | 6 mm ² | Rated voltage | 500 V |
| Rated DC voltage | 500 V | Nominal current | 30 A |
| Current at maximum wires | 30 A | Standards | IEC 60947-7-1 |
| Rated impulse withstand voltage | 6 kV | Surge voltage category | III |
| Pollution severity | 3 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000902 | ETIM 9.0 | EC000902 |
| ETIM 10.0 | EC000902 | ECLASS 14.0 | 27-25-01-09 |
| ECLASS 15.0 | 27-25-01-09 | | |

LST_CTVT_3PHASEPEATTB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

