

**VDEFNNPUSHINEAMNETZ****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

With our pre-assembled SET's for instrument transformer wiring you save time and storage costs. We offer various application setups including all relevant accessories and including labeling in one complete package.

**General ordering data**

Version	Test-disconnect terminal, PUSH IN, beige, 6 mm <sup>2</sup> , 30 A, Number of connections: 36, Number of levels: 1
Order No.	<a href="#">8000107863</a>
Type	VDEFNNPUSHINEAMNETZ
GTIN (EAN)	4099986592643
Qty.	1 items
Delivery status	Discontinued
Last order date	2025-05-06T00:00:00+02:00
Alternative product	<a href="#">TABEAMNETZNS</a>

## VDEFNNPUSHINEAMNETZ

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	79 mm	Depth (inches)	3.1102 inch
Height	100 mm	Height (inches)	3.937 inch
Width	170.4 mm	Width (inches)	6.7086 inch
Net weight	875 g		

## Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	beige
Colour of operational elements	Miscellaneous	UL 94 flammability rating	V-0

## System specifications

End cover plate required	No	Number of levels	1
Number of clamping points per level	36	Mounting rail	TS 35
N-function	No	PE function	Yes

## Additional technical data

Snap-on	Yes	Type of mounting	TS 35
---------	-----	------------------	-------

## Conductors for clamping (rated connection)

Connection direction	top	Type of connection	PUSH IN
Number of connections	36	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	6 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	10 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	6 mm <sup>2</sup>
Connection cross-section, stranded, min. 0.5 mm <sup>2</sup>		Wire connection cross-section, solid core, max.	6 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>		

## General

Standards	IEC 60947-7-1	Mounting rail	TS 35
-----------	---------------	---------------	-------

**VDEFNNPUSHINEAMNETZ**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Rating data**

Rated cross-section	6 mm <sup>2</sup>	Nominal current	30 A
Standards	IEC 60947-7-1	Surge voltage category	III
Pollution severity	3		

**Classifications**

ETIM 8.0	EC000902	ETIM 9.0	EC000902
ETIM 10.0	EC000902	ECLASS 14.0	27-25-01-09
ECLASS 15.0	27-25-01-09		

VDEFNNPUSHINEAMNETZ

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

www.weidmueller.com

